

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS

NOTES:

- 1

MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
COVER : PA66, UL94 V0, COLOR - LIGHT GREEN
PUSH BUTTON : PA66, UL94 V0, COLOR - ORANGE
CONTACT : PHOSPHOR BRONZE, NICKEL PLATED
SPRING : STAINLESS STEEL
- 2





MECHANICAL
WIRE STRIPPING LENGTH : 9 - 10 mm
- 3

ELECTRICAL : 16 - 24 AWG
WIRE RANGE : 150V
RATED VOLTAGE : 8A
RATED CURRENT : >2000 M Ohm (500V DC)
INSULATION RESISTANCE
- 4



OPERATING TEMPERATURE RANGE : -40°C TO +105°C
- 5

TOLERANCE NOT CUMULATIVE

56.80	32	3-2385013-2
53.30	30	3-2385013-0
49.80	28	2-2385013-8
46.30	26	2-2385013-6
42.80	24	2-2385013-4
39.30	22	2-2385013-2
35.80	20	2-2385013-0
32.30	18	1-2385013-8
28.80	16	1-2385013-6
25.30	14	1-2385013-4
21.80	12	1-2385013-2
18.30	10	1-2385013-0
14.80	8	2385013-8
11.30	6	2385013-6
7.80	4	2385013-4
DIM A	NO. OF POS	TE PN



2:1
2385013-3 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13JAN2022 SHRICHARANA B	TE Connectivity NAME TERMINAL BLOCK, DUAL ROW, SPRING PLUG PITCH 3.5mm		
DIMENSIONS: mm		CHK 13JAN2022 SUBHASREE S			
		APVD 13JAN2022 PRASHANTH S			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-32299			
		APPLICATION SPEC 114-32242	SIZE A 3		
MATERIAL 1		WEIGHT -	CAGE CODE 00779		
FINISH 1		DRAWING NO C-2385013			RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1		SHEET 1 OF 1
					REV A