

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS

NOTES:

1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
PUSH BUTTON : PA66, UL94 V0, COLOR - ORANGE
CONTACT : COPPER ALLOY, TIN PLATED
SPRING : STAINLESS STEEL


2. MECHANICAL
WIRE STRIPPING LENGTH : 7 - 8 mm

3. ELECTRICAL
WIRE RANGE : 20 - 28 AWG
RATED VOLTAGE : 150V
RATED CURRENT : 4A
INSULATION RESISTANCE : >2000 M Ohm (500V DC)

4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

5 TOLERANCE NOT CUMULATIVE

40.60	16	1-2385001-6
38.10	15	1-2385001-5
35.60	14	1-2385001-4
33.10	13	1-2385001-3
30.60	12	1-2385001-2
28.10	11	1-2385001-1
25.60	10	1-2385001-0
23.10	9	2385001-9
20.60	8	2385001-8
18.10	7	2385001-7
15.60	6	2385001-6
13.10	5	2385001-5
10.60	4	2385001-4
8.10	3	2385001-3
5.60	2	2385001-2
DIM A	NO. OF POS	TE PN



2385001-3 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11JAN2022 SHRIC HARANA B	TE Connectivity TERMINAL BLOCK, SPRING PLUG, PITCH 2.5mm		
DIMENSIONS: mm		CHK 11JAN2022 SUBHASREE S			
		APVD 11JAN2022 PRASHANTH S			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-32299			
		APPLICATION SPEC 114-32242	NAME		
MATERIAL		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2385001
FINISH		RESTRICTED TO			
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV A	

