

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS





NOTES:

1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
CONTACT : COPPER ALLOY, TIN PLATED

2. ELECTRICAL
RATED VOLTAGE : 300V
RATED CURRENT : 10A
INSULATION RESISTANCE : >2000 M Ohm (500V DC)


3. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

4 TOLERANCE NOT CUMULATIVE



76.81	20	2-2385005-0
73.00	19	1-2385005-9
69.19	18	1-2385005-8
65.38	17	1-2385005-7
61.57	16	1-2385005-6
57.76	15	1-2385005-5
53.95	14	1-2385005-4
50.14	13	1-2385005-3
46.33	12	1-2385005-2
42.52	11	1-2385005-1
38.71	10	1-2385005-0
34.90	9	2385005-9
31.09	8	2385005-8
27.28	7	2385005-7
23.47	6	2385005-6
19.66	5	2385005-5
15.85	4	2385005-4
12.04	3	2385005-3
8.23	2	2385005-2
DIM A	NO. OF POS	TE PN

RECOMMENDED PCB LAYOUT



2385005-3 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12JAN2022 SHRICHARANA B	 TE Connectivity		
DIMENSIONS: mm		CHK 12JAN2022 SUBHASREE S			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 12JAN2022 PRASHANTH S			
PRODUCT SPEC 108-32299		NAME			
APPLICATION SPEC 114-32242		TERMINAL BLOCK, 90 DEG HEADER, PITCH 3.81mm, TAIL LENGTH 3.5mm			
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO
FINISH		-	A3	00779	©-2385005
CUSTOMER DRAWING		SCALE	5:1	SHEET	1 OF 1
		REV	A		