


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS






NOTES:

- 1 MATERIALS & FINISH
 HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
 CONTACTS : COPPER ALLOY, TIN PLATED

2. ELECTRICAL
- | | |
|-----------------------|-------------------------|
| RATED VOLTAGE | : 150V |
| RATED CURRENT | : 8A (UG B) |
| INSULATION RESISTANCE | : >2000 M Ohm (500V DC) |

3. OPERATING TEMPERATURE RANGE : -40°C TO +105°C


- Δ_4 TOLERANCE NOT CUMULATIVE



2385014-3 AS SHOWN

56.80	32	3-2385014-2
53.30	30	3-2385014-0
49.80	28	2-2385014-8
46.30	26	2-2385014-6
42.80	24	2-2385014-4
39.30	22	2-2385014-2
35.80	20	2-2385014-0
32.30	18	1-2385014-8
28.80	16	1-2385014-6
25.30	14	1-2385014-4
21.80	12	1-2385014-2
18.30	10	1-2385014-0
14.80	8	2385014-8
11.30	6	2385014-6
7.80	4	2385014-4
DIM A	NO. OF POS	TE PN

RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14 JAN 2022 SHRICHARANA B		TE Connectivity				
		CHK 14 JAN 2022 SUBHASREE S						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL BLOCK, DUAL ROW, 90 DEG HEADER, PITCH 3.5mm -				
		APVD 14 JAN 2022 PRASHANTH S						
		PRODUCT SPEC 108-32299						
		APPLICATION SPEC 114-32242						
MATERIAL 		FINISH 		SIZE A3	CAGE CODE 00779	DRAWING NO C-2385014	RESTRICTED TO -	
CUSTOMER DRAWING						SCALE 5:1	SHEET 1 OF 1	REV A