



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS

NOTES:

- 1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
CONTACT : BRASS, TIN PLATED
2. ELECTRICAL
RATED VOLTAGE : 150V
RATED CURRENT : 8A (UG B)
INSULATION RESISTANCE : >2000 M Ohm (500V DC)
3. OPERATING TEMPERATURE RANGE : -40°C TO +105°C
- 4 TOLERANCE NOT CUMULATIVE



2385015-3 AS SHOWN

56.8	32	3-2385015-2
53.3	30	3-2385015-0
49.8	28	2-2385015-8
46.3	26	2-2385015-6
42.8	24	2-2385015-4
39.3	22	2-2385015-2
35.8	20	2-2385015-0
32.3	18	1-2385015-8
28.8	16	1-2385015-6
25.3	14	1-2385015-4
21.8	12	1-2385015-2
18.3	10	1-2385015-0
14.8	8	2385015-8
11.3	6	2385015-6
7.8	4	2385015-4
DIM A	NO. OF POS	TE PN

RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14 JAN 2022 SHRICHARANA B	TE Connectivity TERMINAL BLOCK, DUAL ROW, 180 DEG HEADER, PITCH 3.5		
DIMENSIONS: mm		CHK 14 JAN 2022 SUBHASREE S			
		APVD 14 JAN 2022 PRASHANTH S			
		PRODUCT SPEC 108-32299			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-32242	NAME		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2385015
MATERIAL 1		FINISH 1	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV A