




38.8

Ø37.4





TITLE: 09POS,PLUG,SOCKET,24SZ,RD SEAL,SRA,DURAMATE AHDP



	AHDP06-2	4-91SR-	SRA					
	PART N	IUMBEF	3		DE	SCRIPTION		ITEM
QUANTITY			MAT	ERI	ALS LI	ST		
UNLESS OTHERV		SIGN	NATURES	DATE	Λ	mnha		
All dimensions at 2) Tolerances are a PL DEC ±0.30		DRAWN:	IAN.XIAO	13NOV20	Amphenol			
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:	ORION.LI	16NOV20	Sine Systems - www.amphenol-sine.com			
3) Note reference =	- X	ENGINEER:				44724 Morley Drive Clinton Township, MI 480	n36	
MATERIAL SPECIFICAT	TIONS:	APPROVAL:	TOMMY.XIE	17NOV20	Cilition Township, Wii 48036			
		CUSTOMER:) c	9POS,PLUG,SOCKE	T,24SZ,	
			NG IS SUPPLIED		RD	SEAL,SRA,DURAMA	ATE AHDP	
PROCESS SPECIFICAT	TIONS:	SPECIFICATION SHOWN HERI THE AMPHEN OF REPRODU	EON ARE THE P	ORMANCE DATA PROPERTY OF TION. NO RIGHTS PLIED. ALL	B C- AHDP06-24-91SR-SRA A		A1	
NEXT ASS'Y:			RING VARIATIO	NS.	SCALE: NONE		SHEET 1 O	1

2. MODIFICATIONS: SMOOTH ADAPTER;

REDUCED DIA. WIRE SEAL FOR SIZE 12 & SIZE 16;

3. SPECIFICATIONS:

3.1 OPERATING TEMPERATURE: -55°C TO +125°C.

3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.

3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.

3.4 MOISTURE RESISTANCE: IP67 & IP69K (MATED CONDITION).

3.5 MATING CYCLE DURABILITY: 100 CYCLES

3.6 RoHS COMPLIANT

4. MATING PART: AHDP04-24-91P* -XXX (* = SEAL TYPE ,XXX = ALL MODIFICATIONS).

5. CONTACTS 4 AND 5 ARE INTERNALLY CONNECTED.(BUILT-IN BRIDGE).

 $\stackrel{\frown}{6}$. CAVITY 5 IS WITH CONTACT SIZE 16 AND THE GROMMENT IS SEAL.

7. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

8. CONTACT SIZE AND WIRE RANGE:

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	TYPICAL WIRE RANGE	CURRENT RATING
8	3.43mm (.135in)	5.59mm (.220in)	8-10AWG (10.0-5.0mm²)	60AMPS
12	2.46mm (.097in)	4.01mm (.158in)	10-14AWG (6.0-2.0mm²)	25AMPS
16	1.35mm (.053in)	3.05mm (.120in)	14-20AWG (2.0-0.5mm²)	13AMPS

AT Series™ - Contact Size 16 Options

Machined Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined		
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined		
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined		
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined		
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined		
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined		
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined		
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined		
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined		
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined		
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined		
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined		

Tooling - Machined Contacts					
Part	Part Number	Description			
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)			
3	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)			

	Contact Removal Tools					
Part	Part Number	Description				
3	ATRT-100	Used for removal of contacts for A Series™ products				
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16				
	A114017	Sealing Plug, Size 16, White				

Stamped & Formed Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Type		
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-16	Stamped & Formed		
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed		
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed		
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed		
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed		
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed		
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed		
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed		
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed		
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed		
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed		
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed		
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed		
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed		
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed		
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed		

Tooling - Stamped & Formed Contacts				
Part	Part Number	Description		
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)		
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)		
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)		
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)		
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)		
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)		
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)		

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021

MagnaMate™ ATHP - DuraMate™ AHDP - DuraMate™ AHDM Series - Contact Size 12 Options

Machined Contacts, Sockets & Pins					
Part Number	Description	Size	AWG	Type	
AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined	
AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined	
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined	
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined	
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined	
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined	

DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective					
Part Number	Description	Size	AWG	Туре	
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined	
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined	

Tooling - Machined Contacts					
Part	Part Number	Description			
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)			
33	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)			

Contact Removal Tools					
Part	Part Number	Description			
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12			
	A114017	Sealing Plug, Size 12, White			

Stamped & Formed Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed		
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed		
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed		
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed		
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed		
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed		
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed		
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed		

Tooling - Stamped & Formed Contacts					
Part	Part Number	Description			
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)			
	MFX-3985	Crimp Die - Size 12 (S&F contacts only) 10-12AWG -02XX Series			
*	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)			
	ATT-12-01	Hand Crimp Tool - Size 12, 10AWG (S&F contacts only)			

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 01/2022

DuraMate™ ATHD Series™ - Contact Size 8 Options

Machined Contacts, Pins and Sockets					
Part Number	Description	Size	AWG	Туре	Amps
AT60-204-08141	Male Contact - Pin, Copper Alloy, Nickel-Plated	8	8-10	Machined	60A
AT62-203-08141	Female Contact - Socket, Copper Alloy, Nickel-Plated		8-10	Machined	60A

Tooling - Machined Contacts					
Part	Part Number	Description			
	WA23	Heavy Duty Pneumatic Crimp Tool -Uses Universal Positioner Part No. WA23-101DA and Crimp Locator MFX-3961			
	WA23-2	Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 8			
Variety by Barrier B	WA23-10	Contact Locator, Size 8			
NAM	96-978-22	Crimper and Dies -for Size 10mm²-185mm² Wires			

Contact Removal Tools				
Part	Part Number	Description		
	AT114008	Contact Removal Tool, Plastic, Size 8, 8-10AWG		