






FEMALE PLUG M8 STRAIGHT



NOTES:
RATED VOLTAGE: 3 contacts 60V AC/DC
4 and 5 contacts 30V AC/DC
CURRENT RATING: 3, 4, 5 contacts 3A
PROTECTION CLASS: IP 67
TEMPERATURE: -25°C / +80°C

CONTACTS POSITION FRONT VIEW:							
		3 CONTACTS		4 CONTACTS		5 CONTACTS	
FEMALE							
	CONNECTIONS	PIN	WIRE	PIN	WIRE	PIN	WIRE
		1	BROWN	1	BROWN	1	BROWN
		3	BLUE	2	WHITE	2	WHITE
		4	BLACK	3	BLUE	3	BLUE
			4	BLACK	4	BLACK	
					5	GREY	
CODING ACCORDING TO IEC 61076-2-104							



FOR OPTIONS SEE - NUMERICAL CODE - ON SHEET 2

8	2	I/D CARRIER (SEE MATRIX)	---	---
7	1	LABEL YELLOW	VINYL	---
	-	PRINTING FOR CABLES Ixx	---	---
6	-	CABLE	SEE SHEET 2	---
5	-	OVERMOULDING	TPU	SEE SHEET 2
4	1	COUPLING NUT M8 FEMALE	BRASS	SEE SHEET 2
3	1	INSERT FEMALE BLACK	TPU	---
2	1	O-RING RED	FKM	---
1	3 / 4 / 5	CONTACT M8 FEMALE	COPPER	SELECTIVE Au OVER Ni
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

FUNCTIONAL SYMBOLS FA = 0 FE = 0 FV = 0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC: MATRIX UPDATED				molex								
	mm		2:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)				M8 SINGLE ENDED FEMALE STRAIGHT												
	ANGULAR TOL ± °																
	4 PLACES ±		EC NO: 670691				PRODUCT CUSTOMER DRAWING										
	3 PLACES ±		DRWN: RSCHIEBER 2021/07/19														
	2 PLACES ±		CHK'D: RSILLER 2021/07/19														
	1 PLACE ±		APPR: RSILLER 2021/07/19				INITIAL REVISION:										
	0 PLACES ±		DRWN: AKONDRACIUK 2017/02/16														
		APPR: MIWASIECZKO 2017/11/16															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
						A3-SIZE		120086		1200860594		PSD		000		A8	
										MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
										SEE SHEET 3-4		GENERAL MARKET		1 OF 4			

F

E



C

BA

FORMAT: master-lb-prod-A3 REVISION: J DATE: 2020/01/14	9	8	7	6	5	4	3	2	1
--	---	---	---	---	---	---	---	---	---

