



NOTES, UNLESS OTHERWISE SPECIFIED:
 The CT-2600/L and CT-2600/LINT Battery Operated Crimping Tools are designed to crimp #8 AWG - #2 AWG Panduit terminals, disconnects and splices.

The CT-2600/L and CT-2600/LINT Tools include:

- 1 Battery Operated Crimping Tool (with Battery)
- 1 Spare Battery
- 1 Battery Charger
- 1 Tool Case

Weight: (including battery) 4.0 lbs. (1,8 kg)
 Dimensions: (13.25 L x 2.87 H x 4.5 W) IN with battery
 (337 L x 73 H x 114 W) mm

Crimping Time: 4 seconds
 Crimping Force: 4 tons (35 kN)
 CT-2600/L and CT-2600/LINT Battery Operated Crimping Tools are to be used with the following dies:
 CD-2600-P2, CD-2600-P4, CD-2600-P6, CD-2600-P8,
 CD-2600-PV2, CD-2600-PV4, CD-2600-PV6 and CD-2600-PV8.
 The dies are sold separately.

The operation manual for the CT-2600/L and CT-2600/LINT tools, plus die inserts can be found at: www.panduit.com

Replacement Batteries and Battery Chargers are sold separately.

- CT-LIBCMK2AH (2 Ah) Replacement Battery Cartridge
- CT-LIBCMK3AH (3 Ah) Replacement Battery Charger
- CT-LIBCMK4AH (4 Ah) Replacement Battery Cartridge
- CT-CHRMK120V Replacement Battery Charger
- CT-CHRMK230VINT Replacement Battery Charger for Europe
- CT-CHRMK12VDC Replacement Battery Charger (Automotive)

PART NUMBER CT-2600/L & CT-2600/LINT	PACKAGING SPEC N/A
PRODUCT SPEC TS28132A01	WORK INSTRUCTION N/A
INSPECTION INSTRUCTION NUMBER N/A	FMEA & CONTROL PLAN NUMBER N/A

TITLE CD, CT-2600/L & CT-2600/LINT TOOL DRAWING	
CONTROL DRAWING	
ITEM REVISION NAME R28124AA/01	PANDUIT
DATASET FILE NAME R28124AA/01	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
.X ±	.XXX ±
.XX ±	ANGLES ±
THIRD ANGLE PROJECTION	
DRAWN BY	DATE
CHK	SCALE
DRAWING NUMBER: TP28124B01	
SHT 1 OF 1	
SIZE B	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01	06/12/2020	HPR	BJPU	HPR	CONVERTED THE DRAWING FROM MSWORD TO TEAM CENTER, CORRECTED THE WIRING RANGE FROM #(10 - 22) AWG to #(8 - 2)AWG, ADDED NEW BATTERY AND CHARGER	081492
00	07/21/2016	BLR	BJPU	JADE	RELEASED	009767

N:\GLOBAL_BSIZE