





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASED	9/10/13	B.ZHANG
B	ECN 7893: OVERALL LENGTH WAS 1.42 [36.06]	4/3/15	D_DESJARDIN
C	ECN 8014: OVERALL DIMENSION WAS 1.441 [36.60], ADDED NOTES	7/13/15	D.FRISIELLO



RECOMMENDED
PANEL OPENING



"J1"
2X USB TYPE A JACK
30μ SELECTIVE GOLD PLATED CONTACT
NICKEL PLATED SHELL



NOTES:

- ADAPTER HOUSING: ABS, UL94V-0 RATED
- ADAPTER SHIELDING: BRASS, NICKEL PLATED
- PCB: GLASS FIBER EPOXY; FR-4, UL94 V-0
- USB CONNECTORS MEET USB2.0 STANDARD
- OPERATING TEMPERATURE: -20°C~+60°C
- ADAPTER SHALL BE TESTED FOR CONTINUITY.
- ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY B.ZHANG	1/7/13				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY F.MAO	9/10/13	CATEGORY USB			
	APPROVED BY T.LU	9/10/13	PRODUCT DESCRIPTION ADPT, USB KEYSTONE A-A			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. UADKEY-AA	REV. C
			SCALE: NONE	CAD FILE: UADKEY-AA.SLDDRW	SHEET 1 OF 1	