



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECO-11-005150	28MAR2011	RK	HMR
	BA	NEW PRODUCT INTRODUCTION	16JUN2022	LG	AP


FOR FURTHER INFORMATION SEE DATA SHEET FOR
CBT SERIES-CARBON COMPOSITION RESISTORS



RoHS Compliant



SCALE 2:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH.M 16SEP2008		TE Connectivity						
DIMENSIONS: mm		CHK PRAKASH.S 16SEP2008								
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD STEPHEN.P 16SEP2008		NAME CARBON COMPOSITION RESISTORS TYPE CBT25 SERIES					
	0 PLC ±0.2 1 PLC ±0.1 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±5°		PRODUCT SPEC							
			APPLICATION SPEC							
MATERIAL		FINISH		WEIGHT		SIZE A3	CAGE CODE 00779	DRAWING NO C-1625875	RESTRICTED TO	
				CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 4		

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SCHEDULE

TCPN	CATALOGUE NUMBER	PART DESCRIPTION	PART STATUS
1625875-1	CBT25K100R	CBT 1/4 10% 100R	DISCONTINUED
1625875-2	CBT25K10R	CBT 1/4 10% 10R	PRODUCTION
1625875-3	CBT25J4R7	CBT 1/4 5% 4R7	DISCONTINUED
1625875-4	CBT25J100K	CBT 1/4 5% 100K	SUPERSEDED
1625875-5	CBT25J100R	CBT 1/4 5% 100R	PRODUCTION
1625875-6	CBT25J10K	CBT 1/4 5% 10K	PRODUCTION
1625875-7	CBT25J10R	CBT 1/4 5% 10R	PRODUCTION
1625875-8	CBT25J150K	CBT 1/4 5% 150K	SUPERSEDED
1625875-9	CBT25J150R	CBT 1/4 5% 150R	PRODUCTION
1-1625875-0	CBT25J15K	CBT 1/4 5% 15K	PRODUCTION
1-1625875-1	CBT25J15R	CBT 1/4 5% 15R	DISCONTINUED
1-1625875-2	CBT25J1K0	CBT 1/4 5% 1K0	PRODUCTION
1-1625875-3	CBT25J1K5	CBT 1/4 5% 1K5	PRODUCTION
1-1625875-4	CBT25J1M0	CBT 1/4 5% 1M0	SUPERSEDED
1-1625875-5	CBT25J1M5	CBT 1/4 5% 1M5	DISCONTINUED
1-1625875-6	CBT25J1R0	CBT 1/4 5% 1R0	PRODUCTION
1-1625875-7	CBT25J1R5	CBT 1/4 5% 1R5	PRODUCTION
1-1625875-8	CBT25J220K	CBT 1/4 5% 220K	SUPERSEDED
1-1625875-9	CBT25J220R	CBT 1/4 5% 220R	PRODUCTION
2-1625875-0	CBT25J22K	CBT 1/4 5% 22K	PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH.M 16SEP2008	 TE Connectivity		
		CHK PRAKASH.S 16SEP2008			
DIMENSIONS: mm		APVD STEPHEN.P 16SEP2008	NAME CARBON COMPOSITION RESISTORS TYPE CBT25 SERIES		
		PRODUCT SPEC			
		APPLICATION SPEC	SIZE A 3		
MATERIAL		WEIGHT			
		FINISH	CAGE CODE 00779		
			DRAWING NO C-1625875		
			RESTRICTED TO		
			SCALE 4:1		
			SHEET 2 OF 4		
			REV BA		
CUSTOMER DRAWING					

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SCHEDULE

TCPN	CATALOGUE NUMBER	PART DESCRIPTION	PART STATUS
2-1625875-1	CBT25J22R	CBT 1/4 5% 22R	PRODUCTION
2-1625875-2	CBT25J2K2	CBT 1/4 5% 2K2	PRODUCTION
2-1625875-3	CBT25J2M2	CBT 1/4 5% 2M2	DISCONTINUED
2-1625875-4	CBT25J2R2	CBT 1/4 5% 2R2	PRODUCTION
2-1625875-5	CBT25J330K	CBT 1/4 5% 330K	SUPERSEDED
2-1625875-6	CBT25J330R	CBT 1/4 5% 330R	PRODUCTION
2-1625875-7	CBT25J33K	CBT 1/4 5% 33K	PRODUCTION
2-1625875-8	CBT25J33R	CBT 1/4 5% 33R	PRODUCTION
2-1625875-9	CBT25J3K3	CBT 1/4 5% 3K3	PRODUCTION
3-1625875-0	CBT25J3M3	CBT 1/4 5% 3M3	SUPERSEDED
3-1625875-1	CBT25J3R3	CBT 1/4 5% 3R3	PRODUCTION
3-1625875-2	CBT25J470K	CBT 1/4 5% 470K	SUPERSEDED
3-1625875-3	CBT25J470R	CBT 1/4 5% 470R	PRODUCTION
3-1625875-4	CBT25J47K	CBT 1/4 5% 47K	PRODUCTION
3-1625875-5	CBT25J47R	CBT 1/4 5% 47R	PRODUCTION
3-1625875-6	CBT25J4K7	CBT 1/4 5% 4K7	PRODUCTION
3-1625875-7	CBT25J4M7	CBT 1/4 5% 4M7	SUPERSEDED
3-1625875-8	CBT25J680K	CBT 1/4 5% 680K	SUPERSEDED
3-1625875-9	CBT25J680R	CBT 1/4 5% 680R	PRODUCTION
4-1625875-0	CBT25J68K	CBT 1/4 5% 68K	PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2

1 PLC ±0.1

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±5°

MATERIAL

FINISH

DWN
SUBHASH.M
16SEP2008

CHK
PRAKASH.S
16SEP2008

APVD
STEPHEN.P
16SEP2008

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME
CARBON COMPOSITION RESISTORS
TYPE CBT25 SERIES

SIZE
A 3

CAGE CODE
00779

DRAWING NO
C-1625875

RESTRICTED TO

SCALE
4:1

SHEET
3 OF 4

REV
BA

TE Connectivity

1470-19 (3/13)

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SCHEDULE

TCPN	CATALOGUE NUMBER	PART DESCRIPTION	PART STATUS
4-1625875-1	CBT25J68R	CBT 1/4 5% 68R	PRODUCTION
4-1625875-2	CBT25J6K8	CBT 1/4 5% 6K8	PRODUCTION
4-1625875-3	CBT25J6R8	CBT 1/4 5% 6R8	PRODUCTION
4-1625875-4	CBT25K100K	CBT 1/4 10% 100K	PRODUCTION
4-1625875-5	CBT25J120K	CBT 1/4 5% 120K	DISCONTINUED
4-1625875-6	CBT25J100RT	CBT 1/4 5% 100R TAPED & REELED	DISCONTINUED
4-1625875-7	CBT25K220K	CBT 1/4 10% 220K	PRODUCTION
4-1625875-8	CBT25K330K	CBT 1/4 10% 330K	PRODUCTION
4-1625875-9	CBT25K470K	CBT 1/4 10% 470K	PRODUCTION
5-1625875-0	CBT25K680K	CBT 1/4 10% 680K	PRODUCTION
5-1625875-1	CBT25K150K	CBT 1/4 10% 150K	PRODUCTION
5-1625875-2	CBT25K4M7	CBT 1/4 10% 4M7	PRODUCTION
5-1625875-3	CBT25K1M0	CBT 1/4 10% 1M0	PRODUCTION
5-1625875-4	CBT25K3M3	CBT 1/4 10% 3M3	PRODUCTION
5-1625875-5	CBT25K110K	CBT 1/4 10% 110K	PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2

1 PLC ±0.1

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±5°

MATERIAL

FINISH

DWN
SUBHASH.M
16SEP2008

CHK
PRAKASH.S
16SEP2008

APVD
STEPHEN.P
16SEP2008

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME
CARBON COMPOSITION RESISTORS
TYPE CBT25 SERIES

SIZE
A 3

CAGE CODE
00779

DRAWING NO
C-1625875

RESTRICTED TO

SCALE
4:1

SHEET
4 OF 4

REV
BA

TE Connectivity

1470-19 (3/13)