




NOTES

1. 製品詳細寸法については図面 **545481000/PSD/001** を参照下さい。
RE DETAILED DIMENSION, SEE **545481000/PSD/001**
2. 梱包数量：3000個／リール
NUMBER OF CONNECTORS：3000PCS／REEL
3. リードテープ長さ LEAD TAPE LENGTH
4. トップテープの剥離強度： 0.1N ～ 1.3N(10gf ～ 130gf)
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE：0.1N ～ 1.3N(10gf ～ 130gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED , DURING TRANSPORTATION.
5. 材料(MATERIAL)
キャリアテープ(CARRIER TAPE)：ポリプロピレン(POLYPROPYLENE)
トップテープ(TOPTAPE)：PET , PE , PEF
リール(REEL)：ポリスチレン (P S) <リサイクル材を含む>
POLYSTYRENE(PS) <RECYCLE MATERIAL CONTAINED>
6. 本製品は **5 4 5 4 8 - * * 9 1** の鉛フリー (部分金メッキ) 品である。
THIS PRODUCT IS LEAD FREE OF 54548-**91 (SELECTIVE GOLD).



54548-**72		MODEL No.	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:	
DIMENSION UNITS mm		SCALE NTS	
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 710011 DRWN: NARENC CHK'D: YNAITO APPR: SHOSHIKAWA	
ANGULAR TOL ± 3.0°		2022/05/30 2022/06/10 2022/06/10	
4 PLACES ±		INITIAL REVISION:	
3 PLACES ±		DRWN: NARENC	
2 PLACES ±		APPR: SHOSHIKAWA	
1 PLACE ±		2022/05/30 2022/06/10	
0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
THIRD ANGLE PROJECTION		DRAWING A3-SIZE	
SERIES 54548		DOCUMENT NUMBER 545480000	
MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET	
SHEET NUMBER 1 OF 4		DOC TYPE PSD	
DOC PART 001		REVISION A	
GENERAL TOLERANCES (UNLESS SPECIFIED)		10 ^{UNDER} ±0.2	
10 ^{OVER} 30 ^{UNDER} ±0.25		30 ^{OVER} ±0.3	
DOCUMENT STATUS P1		RELEASE DATE 2022/06/10 11:53:05	

F

F

E

E

D

D

C

C

B

B

A

A

引き出し方向
PULL OUT DIRECTION

トッパートープ
TOP TAPE

54548-**25

SECT. X-X

SECT. Y-Y


16mm幅キャリアテープ

16mm WIDTH CARRIER TAPE

16	21.4	17.4	4.3	8.4	9.5	54548-0672	6
			3.8	7.9	9.0	54548-0572	5
			3.3	7.4	8.5	54548-0472	4
キャリアテープ幅 CARRIER TAPE WIDTH	E	D	(C)	(B)	(A)	製品番号 MATERIAL No.	極数 Ck+
				54548-**72		MODEL No.	

GENERAL TOLERANCES (UNLESS SPECIFIED)		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	
		DIMENSION UNITS	SCALE
		mm	NTS
		GENERAL TOLERANCES (UNLESS SPECIFIED)	
ANGULAR TOL ± 3.0°		CURRENT REV DESC:	
4 PLACES ±		EC NO: 710011	
3 PLACES ±		DRWN: NARENC 2022/05/30	
2 PLACES ±		CHK'D: YNAITO 2022/06/10	
1 PLACE ±		APPR: SHOSHIKAWA 2022/06/10	
0 PLACES ±		INITIAL REVISION:	
10 ^{UNDER} ±0.2		DRWN: NARENC 2022/05/30	
10 ^{OVER} 30 ^{UNDER} ±0.25		APPR: SHOSHIKAWA 2022/06/10	
30 ^{OVER} ±0.3		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
		THIRD ANGLE PROJECTION	
		DRAWING	
		SERIES	
		MATERIAL NUMBER	
		CUSTOMER	
		SHEET NUMBER	
		A3-SIZE	
		54548	
		SEE TABLE	
		GENERAL MARKET	
		2 OF 4	

DOCUMENT STATUS	P1	RELEASE DATE	2022/06/10	11:53:05
-----------------	----	--------------	------------	----------



引き出し方向
PULL OUT DIRECTION

54548-**25

トッテープ
TOP TAPE

SECT. Y-Y

SECT. X-X

24mm幅キャリアテープ
24mm WIDTH CARRIER TAPE

24	29.4	25.4	12.3	16.4	17.5	54548-2272	22
			11.3	15.4	16.5	54548-2072	20
			10.3	14.4	15.5	54548-1872	18
			9.3	13.4	14.5	54548-1672	16
			8.8	12.9	14.0	54548-1572	15
			8.3	12.4	13.5	54548-1472	14
			7.8	11.9	13.0	54548-1372	13
			7.3	11.4	12.5	54548-1272	12
			6.3	10.4	11.5	54548-1072	10
			5.8	9.9	11.0	54548-0972	9
			5.3	9.4	10.5	54548-0872	8
			4.8	8.9	10.0	54548-0772	7
キャリアテープ幅 CARRIER TAPE WIDTH	E	D	(C)	(B)	(A)	製品番号 MATERIAL No.	極数 Ckt


54548-**72

MODEL No.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex			
DIMENSION UNITS mm		SCALE NTS		0.5 FPC CONN ZIF HSG ASSY RA BOTTOM CONTACT -LEAD FREE-			
GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL ± 3.0°		PRODUCT CUSTOMER DRAWING			
4 PLACES ±		3 PLACES ±		DOCUMENT NUMBER			
3 PLACES ±		2 PLACES ±		545480000			
2 PLACES ±		1 PLACE ±		PSD			
1 PLACE ±		0 PLACES ±		001			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		A			
10 ^{UNDER}		±0.2		SERIES			
10 ^{OVER} 30 ^{UNDER}		±0.25		A3-SIZE			
30 ^{OVER}		±0.3		54548			
EC NO: 710011		DRWN: NARENC		MATERIAL NUMBER			
CHK'D: YNAITO		APPR: SHOSHIKAWA		CUSTOMER			
INITIAL REVISION:		DRWN: NARENC		SEE TABLE			
APPR: SHOSHIKAWA		2022/05/30		GENERAL MARKET			
2022/06/10		2022/06/10		SHEET NUMBER			
2022/06/10		2022/06/10		3 OF 4			

DOCUMENT STATUS	P1	RELEASE DATE	2022/06/10	11:53:05
-----------------	----	--------------	------------	----------

FORMAT: master-b-prod-A3
REVISION: J1
DATE: 2021/05/01



32mm幅キャリアテープ
32mm WIDTH CARRIER TAPE

32	37.4	33.4	14.3	18.4	19.5	54548-2672	26
			13.3	17.4	18.5	54548-2472	24
キャリアテープ幅 CARRIER TAPE WIDTH	E	D	(C)	(B)	(A)	製品番号 MATERIAL No.	極数 CK+

54548-**72 MODEL No.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex			
DIMENSION UNITS mm		SCALE NTS		0.5 FPC CONN ZIF HSG ASSY RA BOTTOM CONTACT -LEAD FREE-			
GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL ± 3.0°		PRODUCT CUSTOMER DRAWING			
4 PLACES ±		3 PLACES ±		DOCUMENT NUMBER			
3 PLACES ±		2 PLACES ±		545480000			
1 PLACE ±		0 PLACES ±		PSD 001 A			
10 ^{UNDER} ±0.2		10 ^{OVER} 30 ^{UNDER} ±0.25		SHEET NUMBER			
30 ^{OVER} ±0.3		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		4 OF 4			
THIRD ANGLE PROJECTION		DRAWING		SEE TABLE			
A3-SIZE		SERIES		GENERAL MARKET			
54548		MATERIAL NUMBER		CUSTOMER			

