


DCPT (2:1 RATIO) (Yellow/Green Striped)

Single Wall Dual Colour tube. A Premium grade heat shrink tube primarily used for electrical insulation. Has a UL224 approval and several Military related approvals.



PRODUCT DIMENSIONS


SIZE	Inside Diameter as supplied (min) mm (inch) D	Inside Diameter after recovery (max) mm (inch) d	Wall Thickness after recovery (nom) mm (inch) W	Wall Thickness Tolerance after recovery mm (inch)
3/1.5	3.0 (.118)	1.5 (.059)	0.50 (.020)	0.10 (.004)
6/3	6.0 (.236)	3.0 (.118)	0.60 (.024)	0.10 (.004)
8/4	8.0 (.314)	4.0 (.157)	0.65 (.026)	0.10 (.004)
10/5	10.0 (.393)	5.0 (.196)	0.65 (.026)	0.10 (.004)
12/6	12.0 (.472)	6.0 (.236)	0.65 (.026)	0.10 (.004)
19/9	19.0 (.748)	9.0 (.354)	0.75 (.029)	0.15 (.006)
26/13	26.0 (1.023)	13.0 (.511)	0.90 (.035)	0.15 (.006)
38/19	38.0 (1.496)	19.0 (.748)	1.00 (.039)	0.15 (.006)

**DCPT (2:1 RATIO)
(Yellow/Green striped)
STANDARD SIZE REFERENCE
DIMENSIONAL DRAWING**



©2020 TE Connectivity Ltd. family of companies
All Rights Reserved

DIMENSIONS IN
mm (Inch)



SHEET

1 of 2

TITLE

**DCPT (2:1 RATIO) (Yellow/Green striped) –
IRRADIATED MODIFIED POLYOLEFIN SINGLE
WALL HEAT SHRINK TUBING**

NO

DCPT (2:1 RATIO) – Standard sizes

REV

A

A INITIAL REVISION HD 02/02/2021

REV ENGINEERING CHANGE CHK DATE

DCPT (2:1 RATIO) (Yellow/Green Striped)

PRODUCT INFORMATION

General use single wall Polyolefin Tubing.
Shrink Ratio – 2:1
Longitudinal Shrinkage on full recovery – 5 to -10%
Material conforms to TE Specification RW-2056
Standard Colour: Yellow/Green stripe
Flame Retardant

Tubing cut to specific lengths can be supplied from the product sizes
referenced within this drawing.

Cut length tolerances are as per the following table:

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
Up to 9.9mm	±0.5mm
10mm to 24.9mm	±1.0mm
25mm to 54.9mm	±1.5mm
55mm to 99.9mm	±3.0mm
100mm to 149.9mm	±4.0mm
150mm to 499.9mm	±5.0mm
500mm to 1200mm	±12.5mm



TE Connectivity Ltd. family of companies

SHEET

2 of 2

NO.

**DCPT (2:1 RATIO)
(Yellow/Green striped) –
Standard sizes**

REV

A