

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200688189

Status:

Active

Overview:

Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable

Description:

Micro-Change (M12) In-Line Splitter with Knurled Hexnuts, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (90°), WSOR Cable, 0.60m (1.97") Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152210
General	
Product Family	Industrial Tees and Splitters
Series	120009
IP Rating	IP67
Overview	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Micro-Change (M12)
Taxonomy	Industrial Tees and Splitters
Type	Splitter - In-line
UPC	889056131049
Physical	
Color - Cable Jacket	Black
Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	No
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	0.60m
Leg 2 Length	0.60m
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Poles	3 Female/4 Male
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-25°C to +80°C
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	884A31B30M006
Reference - Drawing Numbers	
Sales Drawing	SD-120068-001-001, SD-120068-001-002

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120009 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION