



REVISIONS			
REV	DATE	BY	APPD
-	-	-	-
-	-	-	-
-	-	-	-



1.MISSING DIMENSIONS ACC.TO 2-2399607-1



1.MISSING DIMENSIONS ACC.TO 2-2399607-1

TE-ASSY-NO	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM
2399607-6	L/M	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	M	PA66-GF	AQUA RED	(485)	1	9
			CODE HOUSING	L	PA66-GF	AQUA BROWN		1	8
			FOLLOW 2399607-1	-	-	-		-	1-7
2399607-5	J/K	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	K	PA66-GF	AQUA GREEN	(485)	1	9
			CODE HOUSING	J	PA66-GF	ORANGE		1	8
			FOLLOW 2399607-1	-	-	-		-	1-7
2399607-4	G/H	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	H	PA66-GF	YELLOW	(485)	1	9
			CODE HOUSING	G	PA66-GF	RED		1	8
			FOLLOW 2399607-1	-	-	-		-	1-7
2399607-3	E/F	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	F	PA66-GF	BROWN	(485)	1	9
			CODE HOUSING	E	PA66-GF	GREEN		1	8
			FOLLOW 2399607-1	-	-	-		-	1-7
2399607-2	C/D	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	D	PA66-GF	PURPLE	(485)	1	9
			CODE HOUSING	C	PA66-GF	BLUE		1	8
			FOLLOW 2399607-1	-	-	-		-	1-7
2399607-1	A/B	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	B	PA66-GF	NATURE	(485)	1	9
			CODE HOUSING	A	PA66-GF	BLACK		1	8
			HV INTERLOCK CABLE BRIDGED	-	-	-		1	7
			HV INTERLOCK CABLE	-	-	-		2	6
			FACE SEAL	-	SILICONE	RED		1	5
			BUSBAR FRONT SIDE	-	-	-		2	4
			HEADER TPA	-	PA66-GF	RED		2	3
			FINGER PROTECTION CAP	-	PA66-GF	BLACK		2	2
			HEADER HOUSING 180DEG.2POS	-	AL-ALLOY	NICKEL PLATED		1	1
			WEIGHT (g)						

TE-ASSY-NO	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM
1-2399607-6	L/M	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	M	PA66-GF	AQUA RED	(485)	1	9
			CODE HOUSING	L	PA66-GF	AQUA BROWN		1	8
			FOLLOW 1-2399607-1	-	-	-		-	1-7
1-2399607-5	J/K	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	K	PA66-GF	AQUA GREEN	(485)	1	9
			CODE HOUSING	J	PA66-GF	ORANGE		1	8
			FOLLOW 1-2399607-1	-	-	-		-	1-7
1-2399607-4	G/H	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	H	PA66-GF	YELLOW	(485)	1	9
			CODE HOUSING	G	PA66-GF	RED		1	8
			FOLLOW 1-2399607-1	-	-	-		-	1-7
1-2399607-3	E/F	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	F	PA66-GF	BROWN	(485)	1	9
			CODE HOUSING	E	PA66-GF	GREEN		1	8
			FOLLOW 1-2399607-1	-	-	-		-	1-7
1-2399607-2	C/D	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	D	PA66-GF	PURPLE	(485)	1	9
			CODE HOUSING	C	PA66-GF	BLUE		1	8
			FOLLOW 1-2399607-1	-	-	-		-	1-7
1-2399607-1	A/B	2POS.PIN DIA 14.0 HDR ASSY.180DEG	CODE HOUSING	B	PA66-GF	NATURE	(485)	1	9
			CODE HOUSING	A	PA66-GF	BLACK		1	8
			HV INTERLOCK CABLE BRIDGED	-	-	-		1	7
			HV INTERLOCK CABLE	-	-	-		2	6
			FACE SEAL	-	SILICONE	RED		1	5
			BUSBAR BACK SIDE	-	-	-		2	4
			HEADER TPA	-	PA66-GF	RED		2	3
			FINGER PROTECTION CAP	-	PA66-GF	BLACK		2	2
			HEADER HOUSING 180DEG.2POS	-	AL-ALLOY	NICKEL PLATED		1	1
			WEIGHT (g)						

THIS DRAWING IS A CONTROLLED DOCUMENT.

DATE: 29DEC2021
 CHK: J.L.L.
 DATE: 29DEC2021
 DATE: 29DEC2021


TE Connectivity

2POS.PIN DIA 14.0 HDR ASSY.180DEG
 HVP-HD1400

JOB-160407
 APPLICATION SPEC: 114-160222
 WEIGHT: SEE TABLE
 FINISH SPEC: CUSTOMER DRAWING

SCALE: 2:1
 SHEET: 2 of 4
 REV: A.1


REVISIONS			
REV	DATE	BY	APPD
-	-	-	-
-	-	-	-



printed on 29 Apr 2022 09:37 (Chip) Standard Time from 1452079
 EP

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG: S.TAN 29DEC2021 CHK: L.LI 29DEC2021 APPV: J.VIN 29DEC2021	TE Connectivity
DIMENSIONS: UNITS:	DIMENSIONS UNITS: OPERATING TEMPERATURE: 20.0 °C 25.0 °C 30.0 °C 40.0 °C 50.0 °C 60.0 °C 70.0 °C 80.0 °C 90.0 °C 100.0 °C	PRODUCT SPEC: 10B-160407 APPLICATION SPEC: 114-160222	
MATERIAL: SEE TABLE	FINISH: SPEC 2	WEIGHT: SEE TABLE	SIZE: CASE CODE: DRAWING NO: A0 00779 C=2399607 CUSTOMER DRAWING
		SCALE: 2:1	SHEET 3 of 4 REL: A1

REVISIONS			
REV	DATE	BY	APPD
-	-	-	-
-	-	-	-
-	-	-	-



printed on 20 Apr 2022 09:37 (Only Standard Time from 14:00:00)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DESIGNED BY: S. TAN	DATE: 29DEC2021		TE Connectivity
CHECKED BY: L. LI	DATE: 29DEC2021		
DRAWN BY: J. YIN	DATE: 29DEC2021	NAME: 2POS. PIN D IA 14.0.HDR ASSY.180DEG HVP-HD1400	
MATERIAL: SEE TABLE	FINISH: SPEC 2	SIZE: CASE CODE: DRAWING NO: A0 00779 ©=2399607	
CUSTOMER DRAWING		RESTRICTED TO: -	

SCALE: 2:1 SHEET 4 of 4 REV: A.1