



REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
A	/	Initial version	Wenhong Liu 2022-11-15	SH.Chen 2022-11-15	Rain.Han 2022-11-15





A TYPE



B TYPE

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of AORORA. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of AORORA. © 2019 AORORA

Structure			
No.	Item	Specification	Remark
①	Insulation	White 65um 125C 60V	PET
②		White 65um 125C 60V	
③	Supporting Tape	218um	PET
④	Conductor (Tin plated copper)	Thickness	0.035 ±0.005
		Width	0.3 ±0.03
⑤	Conductor Plating	Plated	Sn(1um) Min
		Plated	/



PART NUMBER:

FF3025-A****-***

No. of Pin

Total Length of FFC

S:The contact surface is on the same side

O:The contact surface is on the opposite side

Dimension 尺寸		
Item	项目	Specification
NO. of conductors	导体芯数	N **
Pitch	间距	P 0.5±0.05
Total Pitch	总间距	SP P*(N-1)±0.07
Total Length	总长度	TL ***±2.0
Insulation Length	绝缘长度	IL ***±2.0
Margin Width	边距	M 0.5±0.07
Total Width	总宽度	W P*(N+1)±0.08
Strip Length	金型长度	S1 **±0.5
Strip Length	金型长度	S2 **±0.5
Reinforeing tape length	补强板长度	B1 **±1.0
Reinforeing tape length	补强板长度	B2 **±1.0
Slanting	线口倾斜度	A ≤0.3
Terminal thickness	插入厚度	T 0.31±0.03
Thickness insulation	线身厚度	ST 0.16±0.05

Special request	
1.Storage of FFC: Temperature: 10~35°C Humidity:30~65%RH	
2.Periods: FFC(Plating Au)12months FFC(Plating Sn)6months	
3.All material must be complied with RoHS	
4.Temperature resistance requirements: -40~125°C	

UNLESS OTHERWISE SPECIFIED TOLERANCES			
X.	±0.30	X. °	± 5'
X.X	±0.25	X.X °	± 4'
X.XX	±0.20	X.XX °	± 3'
X.XXX	±0.15	X.XXX °	± 2'
LINEAR DIMS		ANGLES DIMS	
DWG NO.:	A-NXXXX		
MATERIAL	SEE NOTES		
FINISHED	SEE NOTES		

ANGLE OF PROJECTION	
DOC TYPE	Customer Drw
DRAWN DATE	Wenhong Liu 2022-11-15
DESIGN DATE	Wenhong Liu 2022-11-15
CHECKED DATE	SH.Chen 2022-11-15
APPROVED DATE	Rain.Han 2022-11-15

		Amphenol Aorora Technology (Huizhou) Co.,Ltd	
TITLE: FFC Cable P0.50mm L***mm ***pin			
SIZE	PART NUMBER:	REV.	
A4	FF3025-A****-***	A	
SCALE	1:1	UNIT : mm	SHEET 1 OF 1