


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

- "B" IS MEASURED AT BASE.
- STANDARD LENGTH: 6 ft. (1.83m).
- SEE CURRENT CATALOG FOR PART NUMBER DESIGNATIONS FOR TYPE, COLOR, AND LENGTH.
- DUCT TYPE "H"/"HS" TO BE USED WITH TYPE "HC" COVER. (SEE DWG # 38258-05)
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- TYPE "HS" SOLID WALL DUCT IS AVAILABLE WITH SAME DIMENSIONS, BUT WITHOUT SLOTS IN WALL.
- DUCT IS ALSO AVAILABLE WITH OR WITHOUT MOUNTING HOLES.

PART NO. SYSTEM
CHANNEL EXAMPLE
H S 2X2 LG 6 NM

DUCT TYPE -
SOLID -
WIDTH X HEIGHT -
COLOR -
LENGTH -
NO MOUNTING HOLES -

LENGTH	"L"	"Ls"
6 FT	72.00 ± .18 [1828.8 ± 4.6]	68.00 [1727.20]
2 M	78.74 ± .18 [2000.0 ± 4.6]	76.00 [1930.40]

TITLE		WIRING DUCT - TYPE H & HS DUCT	
CUSTOMER DRAWING			
ITEM REVISION NAME		D38258BC/04	
DATASET FILE NAME		D38258BC_DC/04B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .06 [1.5] .xx ± .03 [.8]		PVC	
.xxx ± ANGLES ± 5 °		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		38258-04	
DRAWN BY	DATE	CHK	SCALE
JCST	11-29-01	JKG	NONE
SHT 1 OF 2			SIZE
			A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

SLOT DIMENSIONS		
NOMINAL DUCT HEIGHT	D	F
2	1.63 ± .04 (41.4 ± 1.0)	.80 ± .04 (20.3 ± 1.0)
3	2.63 ± .03 (66.8 ± .8)	1.00 ± .04 (25.4 ± 1.0)
4	3.63 ± .04 (92.2 ± 1.0)	1.00 ± .04 (25.4 ± 1.0)

PROFILE DIMENSIONS			
NOMINAL DUCT SIZE (W X H)	B	H	T
1.5 x 2	1.75 (44.5)	1.92 (48.8)	.08 (2.0)
1.5 x 3	1.75 (44.5)	3.00 (76.2)	.10 (2.5)
2 x 2	2.17 (55.1)	1.92 (48.8)	.08 (2.0)
2 x 3	2.17 (55.1)	3.00 (76.2)	.10 (2.5)
2 x 4	2.17 (55.1)	4.00 (101.6)	.10 (2.7)
3 x 3	3.25 (82.6)	3.00 (76.2)	.10 (2.5)
3 x 4	3.25 (82.6)	4.00 (101.6)	.11 (2.8)
4 x 4	4.25 (108.0)	4.00 (101.6)	.11 (2.8)

MOUNTING HOLE DIMENSIONS	
NOMINAL DUCT WIDTH	K
1.5	---
2.0	$.50 \pm .01$ (12.7 $\pm$.25)
3.0	$1.00 \pm .01$ (25.4 $\pm$.25)
4.0	$1.50 \pm .01$ (38.1 $\pm$.25)

							TITLE WIRING DUCT – TYPE H & HS DUCT				
							CUSTOMER DRAWING				
							ITEM REVISION NAME D38258BC/04				
							DATASET FILE NAME D38258BC_DC/04B				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ±				

B

A



A

D10100DA/15