

TABLE 3									
	STACK HEIGHT								
SEAM LEAD		SEAF LEA	AD STYLE						
STYLE	-05.0	-05.0 -06.0 -06.5 -07.5							
-02.0	7mm	8mm	8.5mm	9.5mm					
-03.0	8mm	9mm	9.5mm	10.5mm					
-03.5	8.5mm	8.5mm 9.5mm 10mm 11mm							
-06.5	11.5mm	12.5mm	13mm	14mm					
-07.0	12mm	13mm	13.5mm	14.5mm					
-09.0	14mm	14mm 15mm 15.5mm 16.5mm							
-11.0	16mm	16mm 17mm 17.5mm 18.5mm							
-13.0	18mm	19mm	19.5mm	20.5mm					


SECTION "A"-"A	.''
<u>SCALE 4 : 1</u>	_


TABLE 5							
LEAD STYLE	"K"	"L"					
-02.0	.05300590 [1.346] - [1.499]	.04700410 [1.194] - [1.041]					
-03.0	.05300620 [1.346] - [1.575]	.04700380 [1.194] - [0.965]					
-03.5	.05300645 [1.346] - [1.638]	.04700355 [1.194] - [0.902]					


TABLE 6								
No. OF POS	"A"	"B"	"C"	"D"	"E"	"F"		
-10	.696 [17.68]	.622 [15.80]	9	.4500 [11.430]	.4500 [11.430]	.641 [16.28]		
-15	.946 [24.03]	.872 [22.15]	14	.7000 [17.780]	.7000 [17.780]	.891 [22.63]		
-19	1.146 [29.11]	1.072 [27.23]	18	.9000 [22.860]	.9000 [22.860]	1.091 [27.71]		
-20	1.196 [30.38]	1.122 [28.50]	19	.9500 [24.130]	.9500 [24.130]	1.141 [28.98]		
-25	1.446 [36.73]	1.372 [34.85]	24	1.2000 [30.480]	1.2000 [30.480]	1.391 [35.33]		
-30	1.696 [43.08]	1.622 [41.20]	29	1.4500 [36.830]	1.4500 [36.830]	1.641 [41.68]		
-40	2.196 [55.78]	2.122 [53.90]	39	1.9500 [49.530]	1.9500 [49.530]	2.141 [54.38]		
-50	2.696 [68.48]	2.622 [66.60]	49	2.4500 [62.230]	2.4500 [62.230]	2.641 [67.08]		

* PROPRIETARY NOTE * THIS DOCUMENT CONTINUE CONT	520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322
DO NOT SCALE DRAWING	DESCRIPTION: .050 PITCH TERMINAL ARRAY ASSEMBLY
SHEET SCALE: 2:1	DWG. NO. SEAM-XX-XX.X-XXX-XX-X-A-XX-K-XR
	BY: BRATCHER 08-09-2010 SHEET 2 OF 7

TABLE 7								
LEAD STYLE	10-30 POS.	40 POS.	50 POS.					
-02.0, -03.0, -03.5, -06.5, -07.0, - 09.0, -13.0	.006 [0.152]	.009 [0.229]	.009 [0.229]					
-11.0	.0085 [0.216]							







**REVISION CP** 




FIG 9 -GP: GUIDE POST OPTION (ONLY AVAILABLE WITH -02.0 LEAD STYLE, 20, 30, 40, & 50 POSITIONS) (MATES WITH SEAF RIGHT ANGLE ONLY) (SEAM-20-02.0-XXX-06-1-A-GP-XR SHOWN) (SAME AS FIG 1, EXCEPT AS SHOWN) (SOME CENTER FEATURES REMOVED FOR CLARITY)



TABLE 9							
POSITIONS	"V"	"W"					
-20	1.766 [44.86]	1.533 [38.94]					
-30	2.266 [57.56]	2.033 [51.64]					
-40	2.766 [70.26]	2.533 [64.34]					
-50	3.266 [82.96]	3.033 [77.04]					

## **REVISION CP**

 $\langle \mathbb{C} \rangle$ 


TABLE 12

	LEAD STYLE -02.0, -03.0, -03.5										
ROW	K-DOT	"R"				"S	;"				"T"
			10 POS	15 POS	19 POS	20 POS	25 POS	30 POS	40 POS	50 POS	
-04	K-DOT236343005	.236 [5.99]	.230 [5.84]	.355 [9.02]	.455 [11.56]	.480 [12.19]	.605 [15.37]	.730 [18.54]	.980 [24.89]	1.230 [31.24]	.021 [0.53]
-05, -06	K-DOT236343005	.236 [5.99]	.230 [5.84]	.355 [9.02]	.455 [11.56]	.480 [12.19]	.605 [15.37]	.730 [18.54]	.980 [24.89]	1.230 [31.24]	.071 [1.80]
-08	K-DOT325450005	.325 [8.26]	.186 [4.71]	.311 [7.90]	.411 [10.43]	.436 [11.06]	.561 [14.24]	.686 [17.41]	.936 [23.76]	1.186 [30.11]	.076 [1.93]
-10	K-DOT404500005	.404 [10.26]	.146 [3.71]	.271 [6.88]	.371 [9.42]	.396 [10.06]	.521 [13.23]	.646 [16.41]	.896 [22.76]	1.146 [29.11]	.087 [2.21]
-14	K-DOT404500005	.404 [10.26]	.146 [3.71]	.271 [6.88]	.371 [9.42]	.396 [10.06]	.521 [13.23]	.646 [16.41]	.896 [22.76]	1.146 [29.11]	.187 [4.75]
					TABLE	13					

	LEAD STYLE -06.5, -07.0, -09.0, -11.0, -13.0										
ROW	K-DOT	"R"	"S"						"T"		
			10 POS	15 POS	19 POS	20 POS	25 POS	30 POS	40 POS	50 POS	
-04	K-DOT256375005	.256 [6.50]	.220 [5.59]	.345 [8.76]	.445 [11.30]	.470 [11.94]	.595 [15.11]	.720 [18.29]	.970 [24.64]	1.220 [30.99]	.011 [0.28]
-05, -06	K-DOT325450005	.325 [8.26]	.186 [4.71]	.311 [7.89]	.411 [10.43]	.436 [11.06]	.561 [14.24]	.686 [17.41]	.936 [23.76]	1.186 [30.11]	.027 [0.69]
-08	K-DOT404500005	.404 [10.26]	.146 [3.71]	.271 [6.88]	.371 [9.42]	.396 [10.06]	.521 [13.23]	.646 [16.41]	.896 [22.76]	1.146 [29.11]	.037 [0.94]
-10	K-DOT460550005	.460 [11.68]	.119 [3.01]	.244 [6.18]	.344 [8.72]	.369 [9.36]	.494 [12.53]	. <mark>619 [15.71]</mark>	.869 [22.06]	1.119 [28.41]	.059 [1.50]

"U"

TABLE 14							
LEAD STYLE	"U"						
-02.0	.186 [4.72]						
-03.0	.225 [5.72]						
-03.5	.245 [6.22]						
-06.5	.365 [9.27]						
-07.0	.382 [9.70]						
-09.0	.461 [11.71]						
-11.0	.540 [13.72]						
-13.0	.619 [15.72]						



-K: K DOT -K: K DOT (SEAM-20-02.0-XXX-08-1-A-K-XR SHOWN) (SAME AS FIG 1, EXCEPT AS SHOWN) (SOME CENTER FEATURES REMOVED FOR CLARITY)

F:\dwg\misc\mktg\SEAM-XX-XX.X-XXX-XX-A-XX-K-XR-MKT.slddrw

