


- NOTES:
- MATERIALS:
CONTACT: BERYLLIUM COPPER
ALL OTHER METAL PARTS: STAINLESS STEEL
INSULATOR: ULTEM1000
 - FINISH:
CONTACT: GOLD
ALL OTHER METAL PARTS: PASSIVATED
 - MECHANICAL/ENVIRONMENTAL:
DURABILITY: 500 CYCLES
TEMP RANGE: -65°C to +165°C
 - ELECTRICAL:
IMPEDANCE: 50Ω
FREQUENCY RANGE: DC to 110GHz
VSWR(dB): 1.3:1 (-17.69dB)



FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
<div><div><div><div></div><div>A</div></div></div><div>= 0</div></div>	DIMENSION UNITS		SCALE		CURRENT REV DESC:					<div>molex</div>									
	MM/INCH		1:1																
	<div><div><div><div></div><div>E</div></div></div><div>= 0</div></div>	GENERAL TOLERANCES (UNLESS SPECIFIED)								EC NO: 731858 DRWN: KTAGAN 2022/11/04 CHK'D: JBORRELLI 2022/12/14 APPR: LMEIER 2022/12/15					1.0MM PLUG TO 1.0MM JACK ADAPTER				
ANGULAR TOL ± °																			
<div><div><div><div></div><div>P</div></div></div><div>= 0</div></div>	4 PLACES		±		INITIAL REVISION: DRWN: KTAGAN 2022/11/04 APPR: LMEIER 2022/12/15										DOCUMENT NUMBER			DOC TYPE	
	3 PLACES		±							731640000			PSD		000		A		
	2 PLACES		±																
	1 PLACE		±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			<div><div><div><div></div><div>3</div></div></div><div>THIRD ANGLE PROJECTION</div></div> <div><div><div><div></div><div>2</div></div></div><div>DRAWING</div></div> <div>C-SIZE</div>		SERIES		73164		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
	0 PLACES		±																
																1 OF 1			

DOCUMENT STATUS	P1	RELEASE DATE	2022/12/15	18:06:01
-----------------	----	--------------	------------	----------