




P	LTR	DESCRIPTION	DATE	DWN	APVD
	BA	INITIAL DRAWING RELEASE	21OCT2022	LG	AP

FOR FURTHER INFORMATION SEE DATA SHEET FOR
RLW73 SERIES WIDE TERMIAL CURRENT SENSING RESISTOR





RoHS Compliant



SCALE 10:1

RECOMMANDED LAND PATTERN



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LALITH G	21OCT2022	 TE Connectivity	
		CHK ALLAN P	21OCT2022		
		APVD ALLAN P	21OCT2022		
		PRODUCT SPEC			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME WIDE TERMINAL CURRENT SENSING RESISTOR TYPE RLW73 SERIES	
		0 PLC ±0.2		SIZE	
		1 PLC ±0.1		CAGE CODE	
		2 PLC ±		DRAWING NO	
		3 PLC ±		RESTRICTED TO	
		4 PLC ±			
		ANGLES ±			
MATERIAL		FINISH		SCALE	
				25:1	
				SHEET	
				1 OF 2	
				REV	
				BA	


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SCHEDULE			
TCPN	CATALOGUE NUMBER	PART DESCRIPTION	PART STATUS
2176543-1	RLW 73H2FR010TE	RLW 73 H2 1% R010 600ppm 4k RL	PRODUCTION
2176543-2	RLW 73H2FR012TE	RLW 73 H2 1% R012 600ppm 4k RL	PRODUCTION
2176543-3	RLW 73H2FR015TE	RLW 73 H2 1% R015 600ppm 4k RL	PRODUCTION
2176543-4	RLW 73H2FR018TE	RLW 73 H2 1% R018 600ppm 4k RL	PRODUCTION
2176543-5	RLW 73H2FR022TE	RLW 73 H2 1% R022 600ppm 4k RL	PRODUCTION
2176543-6	RLW 73H2FR027TE	RLW 73 H2 1% R027 600ppm 4k RL	PRODUCTION
2176543-7	RLW 73H2FR033TE	RLW 73 H2 1% R033 200ppm 4k RL	PRODUCTION
2176543-8	RLW 73H2FR039TE	RLW 73 H2 1% R039 200ppm 4k RL	PRODUCTION
2176543-9	RLW 73H2FR047TE	RLW 73 H2 1% R047 200ppm 4k RL	PRODUCTION
1-2176543-0	RLW 73H2FR056TE	RLW 73 H2 1% R056 200ppm 4k RL	PRODUCTION
1-2176543-1	RLW 73H2FR068TE	RLW 73 H2 1% R068 200ppm 4k RL	PRODUCTION
1-2176543-2	RLW 73H2FR082TE	RLW 73 H2 1% R082 200ppm 4k RL	PRODUCTION
1-2176543-3	RLW 73H2FR10TE	RLW 73 H2 1% R10 200ppm 4k RL	PRODUCTION
1-2176543-4	RLW 73H2FR12TE	RLW 73 H2 1% R12 200ppm 4k RL	PRODUCTION
1-2176543-5	RLW 73H2FR15TE	RLW 73 H2 1% R15 200ppm 4k RL	PRODUCTION
1-2176543-6	RLW 73H2FR18TE	RLW 73 H2 1% R18 200ppm 4k RL	PRODUCTION
1-2176543-7	RLW 73H2FR22TE	RLW 73 H2 1% R22 200ppm 4k RL	PRODUCTION
1-2176543-8	RLW 73H2FR27TE	RLW 73 H2 1% R27 200ppm 4k RL	PRODUCTION
1-2176543-9	RLW 73H2FR33TE	RLW 73 H2 1% R33 200ppm 4k RL	PRODUCTION
2-2176543-0	RLW 73H2FR39TE	RLW 73 H2 1% R39 200ppm 4k RL	PRODUCTION
2-2176543-1	RLW 73H2FR47TE	RLW 73 H2 1% R47 200ppm 4k RL	PRODUCTION
2-2176543-2	RLW 73H2FR56TE	RLW 73 H2 1% R56 200ppm 4k RL	PRODUCTION
2-2176543-3	RLW 73H2FR68TE	RLW 73 H2 1% R68 200ppm 4k RL	PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

-
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2
1 PLC ±0.1
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

FINISH

-
-

DWN LALITH G 210CT2022

CHK ALLAN P 210CT2022

APVD ALLAN P 210CT2022

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
WIDE TERMINAL CURRENT SENSING
RESISTOR TYPE RLW73 SERIES

-

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 ©=2176543-CD

-

SCALE 25:1 SHEET 2 OF 2 REV BA