


6			5			
ITEM	PART#	DESCRIPTION	QTY	UOM		
A,B	5024390600	2.0 W/B Single Plug Hsg 6Ckt	2	PC		
C	5024380000	2.0 W/B Single Plug Term W/Plt Chain	12	PC		
D	--	WHITE PART ID LABEL	1	PC		

2		1	
FROM	TO	DESCRIPTION	COLOUR
A1	B1	1X22AWG DISC SR-PVC BK UL10002	BLACK
A2	B2	1X22AWG DISC SR-PVC BK UL10002	BLACK
A3	B3	1X22AWG DISC SR-PVC BK UL10002	BLACK
A4	B4	1X22AWG DISC SR-PVC BK UL10002	BLACK
A5	B5	1X22AWG DISC SR-PVC BK UL10002	BLACK
A6	B6	1X22AWG DISC SR-PVC BK UL10002	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2219581060	Clik-Mate 2.0 R-R 6ckt 50mm disc Sn	50±5	15
2219581061	Clik-Mate 2.0 R-R 6ckt 100mm disc Sn	100±5	15
2219581062	Clik-Mate 2.0 R-R 6ckt 150mm disc Sn	150±5	15
2219581063	Clik-Mate 2.0 R-R 6ckt 300mm disc Sn	300±5	15
2219581064	Clik-Mate 2.0 R-R 6ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2022/02/12	A	INITIAL RELEASE	THANUB
DOCUMENT STATUS	P1	RELEASE DATE	2022/12/23 12:42:17

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
	mm	NTS
	CURRENT REV DESC:	
DIVISIONAL SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	ANGULAR TOL ± °	
	4 PLACES	±
	3 PLACES	±
	2 PLACES	±
	1 PLACE	±
	0 PLACES	±
	INITIAL REVISION:	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION
		DRAWING
		SERIES
		MATERIAL NUMBER
		CUSTOMER
		SHEET NUMBER