









COMPACTUS 146WAY HEADER ASSY	560134-1462
PROCUDT NAME	PART No.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: PROPOSED			molex		
mm		1:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)				COMPACTUS 146WAY HEADER ASSY					
ANGULAR TOL ± °									
4 PLACES		±		EC NO: 641997 DRWN: KKATO01					

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGULAR	±3°


molex

COMPACTUS 146WAY HEADER ASSY

PRODUCT CUSTOMER DRAWING


DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
5601340002-SD	PSD	000	A

DOCUMENT STATUS	P1	RELEASE DATE	2020/07/28 04:52:56
-----------------	----	--------------	---------------------




インターフェース毎の端子サイズ及びピン数
TERMINAL SIZE AND PIN COUNT FOR EACH INTERFACE

80WAY INTERFACE		66WAY INTERFACE	
0.5mm TERMINAL	60 PIN	0.5mm TERMINAL	54 PIN
1.0mm TERMINAL	20 PIN	1.0mm TERMINAL	12 PIN



推奨基板寸法 (コネクタ実装面)
RECOMMENDED PCB DIMENSIONS (CONNECTOR MOUNTING SIDE)



- 注記

 - 適合嵌合相手コネクタ(MOLEX製)はFIG.1とする。
 - 材質
ハウジング / 整列板 : PBT-GF30、黒色
端子 : 銅合金 (全端子)
 - 端子表面处理 (全端子)
コンタクト部 : 錫めっき
テール部 : 錫めっき
 - 適合基板厚 : 1.6mm ±0.1
 - 製品重量 : 62g
- NOTES

 - APPLICABLE MATING CONNECTORS(MOLEX) SHALL BE AS FIG.1.
 - MATERIAL
HOUSING / GUIDE PLATE : PBT-GF30%, BLACK
TERMINAL : COPPER ALLOY (ALL TERMINALS)
 - TERMINAL PLATING (ALL TERMINALS)
CONTACT SIDE : Sn
TAIL SIDE : Sn
 - APPLICABLE PCB THICKNESS : 1.6mm ±0.1
 - PRODUCT WEIGHT : 62g

FIG.1

嵌合相手コネクタ MATING CONNECTOR			
ハーネス引出し方向 HARNESS OUTPUT	80WAY	66WAY	
左 LEFT	5601548032	5601526632	
右 RIGHT	5601548022	5601526622	
DOCUMENT STATUS	P1	RELEASE DATE	2020/07/28 04:52:56

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS mm	SCALE 1:1	CURRENT REV DESC: PROPOSED				molex					
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 641997 DRWN: KKATO01 2018/04/26 CHK'D: TIIDA01 2020/07/28 APPR: TOSADA 2020/07/28									
ANGULAR TOL ± °	4 PLACES ±	INITIAL REVISION:				PRODUCT CUSTOMER DRAWING					
2 PLACES ±	3 PLACES ±	DRWN: KKATO01 2018/04/26 APPR: TOSADA 2020/07/28				DOCUMENT NUMBER 5601340002-SD					
1 PLACE ±	0 PLACES ±	THIRD ANGLE PROJECTION				DRAWING A2-SIZE		SERIES 560134	MATERIAL NUMBER 5601341462	CUSTOMER GENERAL	SHEET NUMBER 2 OF 2
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING A2-SIZE		SERIES 560134		MATERIAL NUMBER 5601341462		SHEET NUMBER 2 OF 2	