


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.








FOR APPLICATION


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	20FEB2023	M.G	D.Z

1. MATERIAL: COPPER ALLOY, PER TIN
2. PACKAGE: REEL
3. APPLICATION FEED PITCH: 14MM
4. APPLICABLE WIRE: AWG14, INS DIA Ø3.4-3.8MM
5. RECOMMEND PCB HOLE DIA: Ø2.5-2.6MM
6. RECOMMEND PCB THICKNESS: Ø1.6±0.05MM



2700PC/BOX	2393227-1
PACKAGE QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.GAO 26.09.2021		 TE Connectivity			
		CHK L.CHEN 27.09.2021					
		APVD D.ZHANG 29.09.2021					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME BOARD-IN CONTACT M-TYPE			
		0 PLC ±0.3					
		1 PLC ±0.3					
		2 PLC ±0.3					
		3 PLC ±					
		4 PLC ±		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
		ANGLES ±1°					
MATERIAL 		FINISH  PRE-TIN		WEIGHT 0.154			
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 OF 1	REV A