




- 1
- PHENOLIC PER MIL-M-14, TYPE CFG, BLACK.
- 2
- MATES WITH BLOCK 201345 AND ACCOMODATES TYPE II, TYPE III+, OR TYPE VI #16 PIN OR SOCKET CONTACTS.
- 3
- OPTIONAL SIZE FOR JACKSCREWS.
- 4
- AMP PART NO THIS AREA. DATE CODE AT AMP'S OPTION.

201037-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm (INCHES)

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±0.13 [0.005]

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

MATERIAL

DWN

C. OBERMAN

13 MAR 96

CHK

R. STONE

18 MAR 96

APVD

G. STEINHAUER

11 APR 96

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

NAME

AMP Incorporated

Harrisburg, PA 17105-

BLOCK, FEMALE, 104 POSITION, MINIATURE RECTANGULAR, M SERIES

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-201037

SCALE

2:1

SHEET

1

OF

1