


6		5		4		3		2		1	
ITEM	PART#	DESCRIPTION		QTY	UOM						
A	5023800600	1.25 W/B Single Plg Hsg 6Ckt		1	PC						
B	5023810000	1.25 W/B Single Plg Term W/Plt		6	PC						
C	--	WHITE PART ID LABEL		1	PC						

FROM	TO	DESCRIPTION	COLOUR
A1	--	1X26AWG DISC BK	BLACK
A2	--	1X26AWG DISC BK	BLACK
A3	--	1X26AWG DISC BK	BLACK
A4	--	1X26AWG DISC BK	BLACK
A5	--	1X26AWG DISC BK	BLACK
A6	--	1X26AWG DISC BK	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240921062	CLIK-Mate 1.25 R-S 6ckt 150mm disc Sn	150±5	15
2240921063	CLIK-Mate 1.25 R-S 6ckt 300mm disc Sn	300±5	15
2240921064	CLIK-Mate 1.25 R-S 6ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
 2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
- A THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 0.65 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/11/04	B	INITIAL RELEASE	THANUB
RELEASE STATUS		P1	RELEASE DATE
			2023/05/05 16:46:44

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
	mm	NTS
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
DIVISIONAL SYMBOLS	ANGULAR TOL	± °
	4 PLACES	±
	3 PLACES	±
	2 PLACES	±
	1 PLACE	±
	0 PLACES	±
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
	THIRD ANGLE PROJECTION	DRAWING
	SERIES	MATERIAL NUMBER
	DOCUMENT NUMBER	CUSTOMER
	SHEET NUMBER	

EC NO: 745876
DRWN: THANUB
CHK'D: RDOMZALS
APPR: RDOMZALS

2023/04/11
2023/05/05
2023/05/05

INITIAL REVISION:
DRWN: THANUB
APPR: SKUMAR07

2023/01/15
2023/02/06

molex

SEE TABLE

PRODUCT CUSTOMER DRAWING

2240921060

PSD 000 B

GENERAL MARKET

1 OF 1