

6		5		4		3		2		1	
ITEM	PART#	DESCRIPTION		QTY	UOM						
A	5023801000	1.25 W/B Single Plg Hsg 10Ckt		1	PC						
B	5023810000	1.25 W/B Single Plg Term W/Plt		10	PC						
C	--	WHITE PART ID LABEL		1	PC						

FROM	TO	DESCRIPTION	COLOUR
A1	--	1X26AWG DISC BK	BLACK
A2	--	1X26AWG DISC BK	BLACK
A3	--	1X26AWG DISC BK	BLACK
A4	--	1X26AWG DISC BK	BLACK
A5	--	1X26AWG DISC BK	BLACK
A6	--	1X26AWG DISC BK	BLACK
A7	--	1X26AWG DISC BK	BLACK
A8	--	1X26AWG DISC BK	BLACK
A9	--	1X26AWG DISC BK	BLACK
A10	--	1X26AWG DISC BK	BLACK

PART NUMBER	TITLE	L1	L2(REF)
2240921102	CLIK-Mate 1.25 R-S 10ckt 150mm disc Sn	150±5	15
2240921103	CLIK-Mate 1.25 R-S 10ckt 300mm disc Sn	300±5	15
2240921104	CLIK-Mate 1.25 R-S 10ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

- NOTES
1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
 2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
- THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 0.65 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/11/04	C	INITIAL RELEASE	THANUB
DOCUMENT STATUS	P1	RELEASE DATE	2023/05/05 16:46:44

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
	mm	NTS
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
DIVISIONAL SYMBOLS	ANGULAR TOL	± °
	4 PLACES	±
	3 PLACES	±
	2 PLACES	±
	1 PLACE	±
	0 PLACES	±
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION
	DRAWING	SERIES
A4-SIZE		224092
SEE TABLE		GENERAL MARKET
1 OF 1		