




DIMENSIONS:

A	1.250" ±0.063
B	1.750" ±0.063
C	2.560" MAX.
D	1.320" ±0.063



ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
Iex	@ 27V, 1000Hz, BLK - WHT	0.500mA	Max.
	@ 27V, 1000Hz, BRN - ORG	0.500mA	Max.
Sec. N.L.V	@ 27V, 60Hz, BLK - WHT		
	BLU - RED =	4.280V	±2%
	@ 30V, 60Hz, BRN - ORG		
	GRY - YEL =	4.280V	±2%
DCR	@ 20°C, BLK - WHT =	641.0 Ω	±20%
	@ 20°C, BRN - ORG =	641.0 Ω	±20%
	@ 20°C, BLU - RED =	31.00 Ω	±20%
	@ 20°C, GRY - YEL =	31.00 Ω	±20%
HIPOT	PRIMARY - SECONDARY	750V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND ELECTRONIC DIVISION			
0	RELEASED.	C.I. 08/18/22	MANUFACTURING™ 52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: CHASSIS MOUNT	DWG. NO.
			DATE: 08/18/22	APP'D. BY:	AUDIO TRANSFORMER	842A
				DIMENSIONS: IN(X) MM()		

PH # (519) 886-6181
FAX # (519) 886-9540