


REVISION HISTORY		DATE	APPROVED
REV	DESCRIPTION		
-	NRN 47424	05/23	
			SEE PDM



MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1/2° DECIMAL: X ±.030 X.XX ±.010 XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) HOLE DIMENSIONS ARE IN INCHES (MILLIMETERS) 3) UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE TO MAX. 4) CHAM. 1ST & LAST THREADS 5) CHAM. 1ST & LAST THREADS UNLESS OTHERWISE SPECIFIED 6) DIM. S. TO COMMON CENTERS TO BE CONCENTRIC 7) REMOVE ALL BURRS	SMMP FEMALE R/A TO SMMP FEMALE 12" CABLE ASSEMBLY FOR Ø.047 CABLE	TITLE: 7032-9725	
FINISH:	SEE NOTES					
SURFACE AREA:	N/A					
PROPRIETARY						
THE INFORMATION CONTAINED IN THIS DRAWING IS THE PROPERTY OF AMPHENOL COMMUNICATIONS, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF AMPHENOL COMMUNICATIONS, INC. IS PROHIBITED.		THIRD ANGLE PROJECTION 	DRAWN: KRR 05/10/23 CHECKED: SEE PDM APPROVED: SEE PDM	SIZE: DWG. NO. B 7032-9725	SCALE: 4:1	SHEET 06 OF 1