

<u>NOTES</u>

- A: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND SAFETY MARKING (FOR ONLY APPROVED PRODUCTS) ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B: M3 EMBOSSED, TAPPED AND COUNTERSUNK HOLES (4) FOR CUSTOMER CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 6mm.
- C: REMOTE ON/OFF CONTROL CONNECTOR --- OPTION B2B-XH-AM (JST)

MATCHING HOUSING: XHP-2 (JST)

MATCHING TERMINAL PIN: BXH-001T-P0.6 (JST) OR SXH-001T-P0.6 (JST)

HAND CRIMPING TOOL : YC-110R (JST) OR YRS-110 (JST) MATCHING HOUSING AND TERMINAL PIN --- NOT INCLUDED


WITH THE PRODUCT

ACCESSORIES

* SHORT PIECE (NET 2) FOR SHORTING PURPOSE $(+S\sim+V, -S\sim-V)$: MOUNTED AT TIME OF SHIPMENT.

OPTIONAL MODELS

MODEL	REMOTE ON/OFF CONTROL
HWS100A-*	_
HWS100A-* [/R]	0



(unit : mm)

MODEL NAME HWS100A

TDK-Lambda

A258-02-01B