









MATERIALS AND FINISHES:

BODY, JAM NUT, FLAT WASHER: BRASS
PLATED GOLD

CENTER CONTACT: BERYLLIUM COPPER
PLATED GOLD


INSULATOR: TEFLON

LOCK WASHER: PHOSPHOR BRONZE
PLATED GOLD



RECOMMENDED PAD LAYOUT

BASE WIDTH: .250(6.35) NOM.
BOARD THICKNESS: .062(1.57) NOM.
BOARD MATERIAL: FR4 W/1.0 OZ COPPER
BOTH SIDES



73251-2123	-2120 WITHOUT HARDWARE	ONE PIECE PER BAG	895420090
73251-2122	-2120 W / JAM NUT & FLAT WASHER	TRAY	895420040
73251-2121	-2120 W / JAM NUT & LOCK WASHER	TRAY	895420040
73251-2120	-2120 WITHOUT HARDWARE	TRAY	895420040
PART NO.	DESCRIPTION	PACKAGING	PACKING SPEC

PS-89675-346	PRODUCT SPECIFICATION
MIL-STD-348A, FIG. 310.2	INTERFACE
SPECIFICATION	DESCRIPTION

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/22	09:42:03
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS FA = 0 FC = 0 FD = 0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC: ADD PKG NOTE PER EWR15788-A			molex							
	IN/MM		NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	ANGULAR TOL		± 2.0 °												
	4 PLACES		±					EC NO: 746940			SMA JACK, EDGE MOUNT .062 BOARD, 50 OHMS, EWR-2074 SMA-J/PCB				
	3 PLACES		±		DRWN: CWEI02 2022/09/20										
	2 PLACES		±		CHK'D: YCHENG 2023/05/22										
	1 PLACE		±		APPR: YCHENG 2023/05/22			PRODUCT CUSTOMER DRAWING							
	0 PLACES		±		INITIAL REVISION:										
DRWN: SSS 2003/07/09		SD-73251-212			DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION				
APPR: JWIENER 2010/10/27					PSD		001		A6						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						C-SIZE		73251		SEE TABLE		GENERAL MARKET		1 OF 1	