

MATERIALS AND FINISHES:

SMA JACK BULKHEAD IP68 CONNECTOR:

BODY, CRIMP TUBE, JAM NUT: BRASS
PLATED GOLD

CENTER CONTACT: BERYLLIUM COPPER
PLATED GOLD

INSULATOR: PTFE

LOCK WASHER: PHOSPHOR BRONZE
PLATED GOLD

GASKET: SILICONE RUBBER

PERFORMANCE REQUIREMENTS

FREQUENCY RANGE: 0~12GHz



IMPEDANCE: 50 Ω

WITHSTAND VOLTAGE(AC): 350V @0.5mA

CONTINUITY: 100% TEST




PANEL LEAKAGE: IP68

PACKAGING BY PLASTIC BAG



FLAT

SMA JACK BULKHEAD IP68 CONNECTOR
73251-6610



RECOMMENDED MOUNTING HOLE

73230-6175	2.000±.118	50.80±3.00
73230-6174	4.000±.197	101.60±5.00
73230-6173	6.000±.197	152.40±5.00
73230-6172	8.000±.197	203.20±5.00
73230-6171	10.000±.197	254.00±5.00
73230-6170	12.008±.197	305.00±5.00
PART NO.	IN	MM
	L	

DOCUMENT STATUS	P1	RELEASE DATE	2023/07/13	01:49:57
-----------------	----	--------------	------------	----------

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
FUNCTIONAL SYMBOLS FA=0 FE=0 FP=0 DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: ADD NEW PN.73230-6171, -6172,-6173,-6174,-6175 PER EWR#: 15306-D.				molex CA, SMA JACK BULKHEAD IP68 TO MHF® 4L LK WITH DIA 1.37MM CABLE,50 OHMS,EWR#: 15306-A					
		MM/INCH		4:1											
		GENERAL TOLERANCES (UNLESS SPECIFIED)													
		ANGULAR TOL ± °													
		4 PLACES		±		EC NO: 756278 DRWN: YHUANG11									