

MATERIALS AND FINISHES:

SMA JACK RP BULKHEAD
IP68 CONNECTOR:

BODY, CRIMP TUBE, JAM NUT: BRASS
PLATED GOLD

CENTER CONTACT: BRASS
PLATED GOLD

INSULATOR: PTFE

LOCK WASHER: PHOSPHOR BRONZE
PLATED GOLD

GASKET: SILICONE RUBBER

MHF® I LK CONNECTOR:



CABLE: 1.13MM CABLE

HEAT SHRINK TUBE: PE

PERFORMANCE REQUIREMENTS


FREQUENCY RANGE: 0-6GHz
IMPEDANCE: 50 Ω
WITHSTAND VOLTAGE(AC): 350V @0.5mA
CONTINUITY: 100% TEST
PANEL LEAKAGE: IP68

PACKAGING BY PLASTIC BAG



73230-6255	50.80±3.00	2.00±.118
73230-6254	101.60±6.00	4.00±.236
73230-6253	152.40±6.00	6.00±.236
73230-6252	203.20±6.00	8.00±.236
73230-6251	254.00±6.00	10.00±.236
73230-6250	305.00±6.00	12.00±.236
MOLEX PART NO.	MM	IN
	L	

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/04	06:58:43
-----------------	----	--------------	------------	----------



RECOMMENDED MOUNTING HOLE

FUNCTIONAL SYMBOLS FA = 0 FE = 0 FP = 0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC: ADD NEW LENGTHS				molex CA,SMA JACK RP BULKHEAD IP68 TO MHF® ? LK WITH DIA 1.13MM CABLE,50 OHMS,EWR#: 15301-A								
	MM/INCH		4:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)																
	ANGULAR TOL		± °														
	4 PLACES		±		EC NO: 745951 DRWN: MYLU07 2023/02/20 CHK'D: YHUANG11 2023/04/28 APPR: LCHEN03 2023/05/04		PRODUCT CUSTOMER DRAWING										
	3 PLACES		±														
	2 PLACES		±														
	1 PLACE		±														
	0 PLACES		±		INITIAL REVISION: DRWN: MYLU07 2022/07/25 APPR: LCHEN03 2022/09/22				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION		
									732306250				PSD		000		A3
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
						C-SIZE		73230		SEE TABLE		GENERAL MARKET				1 OF 1	

mo

lex

CA,SMA JACK RP BULKHEAD IP68 TO MHF® ?
LK WITH DIA 1.13MM CABLE,50 OHMS,EWR#: 15301-A

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER
732306250

DOC TYPE
PSD

DOC PART
000

REVISION
A3