

MATERIALS AND FINISHES

BODY BRASS
PLATED NICKEL

CENTER CONTACT BRASS
PLATED GOLD

INSULATOR TEFLON

SHRINK TUBE VERSAFIT 3/16 OR EQUIVALENT

LABEL VERSAFIT 3/16 OR EQUIVALENT

CABLE RG179

PACKAGING BY PLASTIC BAG.








TABLE 2:

73230-5257	48.00±.394	1219.20±10.00
73230-5256	36.00±.315	914.40±8.00
73230-5255	24.00±.197	609.60±5.00
73230-5254	18.00±.118	457.20±3.00
73230-5253	6.00±.040	152.40±1.00
73230-5252	125.00±1.00	3175.00±25.4
73230-5251	120.00±1.00	3048.00±25.4
73230-5250	12.00±.030	304.80±0.76
MOLEX	IN	MM
PART NO.	DIM A	

TABLE 1:

MIL-STD-348A, FIG. 301.1	INTERFACE
SPECIFICATION	DESCRIPTION

DOCUMENT STATUS	P1	RELEASE DATE	2021/10/15	08:17:25
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
 = 0  = 0  = 0 RELEASE		DIMENSION UNITS MM/INCH	
SCALE 3:1		CURRENT REV DESC: ADD SIZE 20.00 REF. CHANGE LABEL TEXT; ADD LABEL:VERSAFIT 3/16 OR EQUIVALENT. REMOVE CUSTOMER P/N.	
GENERAL TOLERANCES (UNLESS SPECIFIED)			
ANGULAR TOL ± 2.0 °		CA BNC PLUG STR TO BNC PLUG STR WITH RG179 CABLE, EWR#14545-A	
4 PLACES ±		EC NO: 680838 DRWN: WANGR2 2021/09/29 CHK'D: MYLU07 2021/10/15 APPR: LCHEN03 2021/10/15	
3 PLACES ±		PRODUCT CUSTOMER DRAWING	
2 PLACES ±		DOCUMENT NUMBER 732305250	
1 PLACE ±		DOC TYPE PSD	
0 PLACES ±		DOC PART 000	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		REVISION A1	
THIRD ANGLE PROJECTION 		SHEET NUMBER 1 OF 1	
DRAWING C-SIZE		SERIES 73230	
MATERIAL NUMBER SEE TABLE 2		CUSTOMER GENERAL MARKET	