











## CIRCUIT CONFIGURATIONS

## CIRCUITE SIZE

## PLUG HOUSING ASSEMBLY




## PLUG HOUSING ASSEMBLY WITH KEY D

## PLUG HOUSING ASSEMBLY WITH KEY AND CLIP SLOT D



|                                                      |  |                                                                                                                                               |  |                                                     |  |
|------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------|--|
| FUNCTIONAL SYMBOLS                                   |  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |  |                                                     |  |
| DIMENSION UNITS                                      |  | SCALE                                                                                                                                         |  | CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE. |  |
| mm                                                   |  | 5:1                                                                                                                                           |  |                                                     |  |
| GENERAL TOLERANCES (UNLESS SPECIFIED)                |  |                                                                                                                                               |  |                                                     |  |
| ANGULAR TOL ± °                                      |  |                                                                                                                                               |  |                                                     |  |
| 4 PLACES                                             |  | ±                                                                                                                                             |  | EC NO: 760095                                       |  |
| 3 PLACES                                             |  | ±                                                                                                                                             |  | DRWN: GOOLAM 2023/08/02                             |  |
| 2 PLACES                                             |  | ±                                                                                                                                             |  | CHK'D: GOOLAM 2023/08/18                            |  |
| 1 PLACE                                              |  | ± 0.3                                                                                                                                         |  | APPR: MRAMAKRISHNA 2023/08/18                       |  |
| 0 PLACES                                             |  | ±                                                                                                                                             |  | INITIAL REVISION:                                   |  |
| DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS |  | THIRD ANGLE PROJECTION                                                                                                                        |  | DRWN: MUM 2019/01/30                                |  |
|                                                      |  | DRAWING                                                                                                                                       |  | APPR: NCSR 2019/07/03                               |  |
|                                                      |  | SERIES                                                                                                                                        |  | DOCUMENT NUMBER                                     |  |
|                                                      |  | E-SIZE 207778                                                                                                                                 |  | 2077780000-SD                                       |  |
|                                                      |  |                                                                                                                                               |  | DOC TYPE                                            |  |
|                                                      |  |                                                                                                                                               |  | PSD                                                 |  |
|                                                      |  |                                                                                                                                               |  | DOC PART                                            |  |
|                                                      |  |                                                                                                                                               |  | 000                                                 |  |
|                                                      |  |                                                                                                                                               |  | REVISION                                            |  |
|                                                      |  |                                                                                                                                               |  | D3                                                  |  |
|                                                      |  |                                                                                                                                               |  | MATERIAL NUMBER                                     |  |
|                                                      |  |                                                                                                                                               |  | SEE TABLE                                           |  |
|                                                      |  |                                                                                                                                               |  | CUSTOMER                                            |  |
|                                                      |  |                                                                                                                                               |  | GENERAL MARKET                                      |  |
|                                                      |  |                                                                                                                                               |  | SHEET NUMBER                                        |  |
|                                                      |  |                                                                                                                                               |  | 1 OF 4                                              |  |


|                 |    |              |            |          |
|-----------------|----|--------------|------------|----------|
| DOCUMENT STATUS | P1 | RELEASE DATE | 2023/08/18 | 10:37:23 |
|-----------------|----|--------------|------------|----------|

BACK VIEW


|                                                            |  |                                                                                                                                               |  |                                  |  |                                                                                                                                                                                 |  |                                |  |                            |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
|------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------|--|----------------------------|--|----------------------------|--|--------------------------------------|--|---------------------|--|---------------------|--|--------------------|--|
| FUNCTIONAL SYMBOLS                                         |  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |  |                                  |  |                                                                                                                                                                                 |  |                                |  |                            |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
| DIVISIONAL SYMBOLS                                         |  | DIMENSION UNITS                                                                                                                               |  | SCALE                            |  | CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE.                                                                                                                             |  |                                |  | <div>molex</div>           |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
|                                                            |  | mm                                                                                                                                            |  | 5:1                              |  |                                                                                                                                                                                 |  |                                |  |                            |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
|                                                            |  | GENERAL TOLERANCES (UNLESS SPECIFIED)                                                                                                         |  |                                  |  | EC NO: 760095<br>DRWN: GOOLAM 2023/08/02<br>CHK'D: GOOLAM 2023/08/18<br>APPR: MRAMAKRISHNA 2023/08/18<br><br>INITIAL REVISION:<br>DRWN: MUM 2019/01/30<br>APPR: NCSR 2019/07/03 |  |                                |  | PLUG ASSEMBLY<br>SQUBA 3.6 |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
|                                                            |  | ANGULAR TOL    ±       °                                                                                                                      |  |                                  |  |                                                                                                                                                                                 |  |                                |  |                            |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
|                                                            |  | 4 PLACES                                                                                                                                      |  | ±                                |  |                                                                                                                                                                                 |  |                                |  | PRODUCT CUSTOMER DRAWING   |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
|                                                            |  | 3 PLACES                                                                                                                                      |  | ±                                |  |                                                                                                                                                                                 |  |                                |  |                            |  |                            |  | DOCUMENT NUMBER<br><br>2077780000-SD |  | DOC TYPE<br><br>PSD |  | DOC PART<br><br>000 |  | REVISION<br><br>D3 |  |
|                                                            |  | 2 PLACES                                                                                                                                      |  | ±                                |  |                                                                                                                                                                                 |  |                                |  |                            |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
| 1 PLACE                                                    |  | ±       0.3                                                                                                                                   |  | MATERIAL NUMBER<br><br>SEE TABLE |  |                                                                                                                                                                                 |  | CUSTOMER<br><br>GENERAL MARKET |  |                            |  | SHEET NUMBER<br><br>2 OF 4 |  |                                      |  |                     |  |                     |  |                    |  |
| 0 PLACES                                                   |  | ±                                                                                                                                             |  |                                  |  |                                                                                                                                                                                 |  |                                |  |                            |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
| DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS |  | THIRD ANGLE PROJECTION                                                                                                                        |  | DRAWING                          |  | SERIES                                                                                                                                                                          |  |                                |  |                            |  |                            |  |                                      |  |                     |  |                     |  |                    |  |
|                                                            |  |                                                          |  | E-SIZE                           |  | 207778                                                                                                                                                                          |  |                                |  |                            |  |                            |  |                                      |  |                     |  |                     |  |                    |  |

D


KEY A, RED COLOR




KEY B, NATURAL COLOR




KEY C, GRAY COLOR




KEY D, YELLOW COLOR



KEY E, BROWN COLOR



KEY F, ORANGE COLOR



| CHARTED DIMENSIONS |              |       |                  |       |               |       |                 |       |                |       |                 |       |
|--------------------|--------------|-------|------------------|-------|---------------|-------|-----------------|-------|----------------|-------|-----------------|-------|
| KEYS               | KEY A<br>RED |       | KEY B<br>NATURAL |       | KEY C<br>GRAY |       | KEY D<br>YELLOW |       | KEY E<br>BROWN |       | KEY F<br>ORANGE |       |
| DIMENSIONS         | H            | I     | J                | K     | L             | M     | N               | O     | P              | Q     | R               | S     |
| CKT 2              | 8.56         | 8.56  | 8.23             | 8.56  | 8.94          | 8.56  | 8.23            | 8.56  | 8.94           | 8.56  | 8.94            | 8.23  |
| CKT 3              | 10.10        | 10.10 | 9.61             | 10.10 | 10.75         | 10.10 | 9.61            | 10.10 | 10.75          | 10.10 | 10.75           | 9.61  |
| CKT 4              | 11.58        | 11.58 | 10.88            | 11.58 | 12.54         | 11.58 | 10.88           | 11.58 | 12.54          | 11.58 | 12.54           | 10.88 |

NOTE: KEYING CONFIGURATIONS WILL REMAINS SAME IN 2 & 3 CKT.

|                    |                                                                                                                                               |                                                                                                       |                                                                    |         |        |                  |                |          |              |          |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------|---------|--------|------------------|----------------|----------|--------------|----------|
| FUNCTIONAL SYMBOLS | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                                                                                                       |                                                                    |         |        |                  |                |          |              |          |
|                    | DIMENSION UNITS                                                                                                                               | SCALE                                                                                                 | CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE.                |         |        | <div>molex</div> |                |          |              |          |
|                    | GENERAL TOLERANCES (UNLESS SPECIFIED)                                                                                                         |                                                                                                       |                                                                    |         |        |                  |                |          |              |          |
| ANGULAR TOL ± °    |                                                                                                                                               |                                                                                                       |                                                                    |         |        |                  |                |          |              |          |
| 4 PLACES           | ±                                                                                                                                             | EC NO: 760095<br>DRWN: GOOLAM 2023/08/02<br>CHK'D: GOOLAM 2023/08/18<br>APPR: MRAMAKRISHNA 2023/08/18 |                                                                    |         |        |                  |                |          |              |          |
| 3 PLACES           | ±                                                                                                                                             |                                                                                                       |                                                                    |         |        |                  |                |          |              |          |
| 2 PLACES           | ±                                                                                                                                             |                                                                                                       |                                                                    |         |        |                  |                |          |              |          |
| 1 PLACE            | ± 0.3                                                                                                                                         |                                                                                                       |                                                                    |         |        |                  |                |          |              |          |
| DIVISIONAL SYMBOLS | 0 PLACES                                                                                                                                      | ±                                                                                                     | INITIAL REVISION:<br>DRWN: MUM 2019/01/30<br>APPR: NCSR 2019/07/03 |         |        | DOCUMENT NUMBER  |                | DOC TYPE | DOC PART     | REVISION |
|                    | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS                                                                                          |                                                                                                       | THIRD ANGLE PROJECTION                                             | DRAWING | SERIES | MATERIAL NUMBER  | CUSTOMER       |          | SHEET NUMBER |          |
|                    |                                                                                                                                               |                                                                                                       |                                                                    | E-SIZE  | 207778 | SEE TABLE        | GENERAL MARKET |          | 3 OF 4       |          |

## PART NUMBER DETAILS

| PART NUMBER DETAILS                                                                                               |                               |                    |                         |         |
|-------------------------------------------------------------------------------------------------------------------|-------------------------------|--------------------|-------------------------|---------|
| WITHOUT KEY P/N                                                                                                   | WIRE STYLE                    | NO. OF<br>CIRCUITS | KEYING<br>CONFIGURATION | COLOR   |
| 2077780002                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | NA                      | BLACK   |
| 2077780003                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | NA                      | BLACK   |
| 2077780004                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | NA                      | BLACK   |
| 2077780005*                                                                                                       | UL1007 / UL1061 OR EQUIVALENT | 5                  | NA                      | BLACK   |
| WITH KEY P/N                     |                               |                    |                         |         |
| 2077780102                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 1                       | RED     |
| 2077780202                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 2                       | NATURAL |
| 2077780302                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 3                       | GRAY    |
| 2077780402                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 4                       | YELLOW  |
| 2077780502                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 5                       | BROWN   |
| 2077780602                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 6                       | ORANGE  |
|                                                                                                                   |                               |                    |                         |         |
| 2077780103                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 1                       | RED     |
| 2077780203                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 2                       | NATURAL |
| 2077780303                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 3                       | GRAY    |
| 2077780403                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 4                       | YELLOW  |
| 2077780503                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 5                       | BROWN   |
| 2077780603                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 6                       | ORANGE  |
|                                                                                                                   |                               |                    |                         |         |
| 2077780104                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 1                       | RED     |
| 2077780204                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 2                       | NATURAL |
| 2077780304                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 3                       | GRAY    |
| 2077780404                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 4                       | YELLOW  |
| 2077780504                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 5                       | BROWN   |
| 2077780604                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 6                       | ORANGE  |
| WITH KEY AND CLIP<br>SLOT P/N  |                               |                    |                         |         |
| 2077781102                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 1                       | RED     |
| 2077781202                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 2                       | NATURAL |
| 2077781302                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 3                       | GRAY    |
| 2077781402                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 4                       | YELLOW  |
| 2077781502                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 5                       | BROWN   |
| 2077781602                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 2                  | 6                       | ORANGE  |
|                                                                                                                   |                               |                    |                         |         |
| 2077781103                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 1                       | RED     |
| 2077781203                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 2                       | NATURAL |
| 2077781303                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 3                       | GRAY    |
| 2077781403                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 4                       | YELLOW  |
| 2077781503                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 5                       | BROWN   |
| 2077781603                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 3                  | 6                       | ORANGE  |
|                                                                                                                   |                               |                    |                         |         |
| 2077781104                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 1                       | RED     |
| 2077781204                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 2                       | NATURAL |
| 2077781304                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 3                       | GRAY    |
| 2077781404                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 4                       | YELLOW  |
| 2077781504                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 5                       | BROWN   |
| 2077781604                                                                                                        | UL1007 / UL1061 OR EQUIVALENT | 4                  | 6                       | ORANGE  |

## PART NUMBER LOGIC (D)

207778 - X X X X

## CIRCUITE SIZE





0 = UL1007/1061 COMPATIBLE  
1 = UL1015 / UL1230 COMPATIBLE

- 1 - 6 KEYS

1 = CLIP SLOT / WITH PANEL MOUNT  
0 = NON-CLIP SLOT / WITHOUT PANEL MOUNT

## SERIES NUMBERS

| WITHOUT KEY P/N                                                                                                   | WIRE STYLE                    | NO. OF<br>CIRCUITS | KEYING<br>CONFIGURATION | COLOR   |
|-------------------------------------------------------------------------------------------------------------------|-------------------------------|--------------------|-------------------------|---------|
| 2077780012                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | NA                      | BLACK   |
| 2077780013                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | NA                      | BLACK   |
| 2077780014                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | NA                      | BLACK   |
| WITH KEY P/N                   |                               |                    |                         |         |
| 2077780112                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 1                       | RED     |
| 2077780212                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 2                       | NATURAL |
| 2077780312                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 3                       | GRAY    |
| 2077780412                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 4                       | YELLOW  |
| 2077780512                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 5                       | BROWN   |
| 2077780612                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 6                       | ORANGE  |
|                                                                                                                   |                               |                    |                         |         |
| 2077780113                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 1                       | RED     |
| 2077780213                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 2                       | NATURAL |
| 2077780313                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 3                       | GRAY    |
| 2077780413                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 4                       | YELLOW  |
| 2077780513                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 5                       | BROWN   |
| 2077780613                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 6                       | ORANGE  |
|                                                                                                                   |                               |                    |                         |         |
| 2077780114                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 1                       | RED     |
| 2077780214                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 2                       | NATURAL |
| 2077780314                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 3                       | GRAY    |
| 2077780414                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 4                       | YELLOW  |
| 2077780514                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 5                       | BROWN   |
| 2077780614                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 6                       | ORANGE  |
| WITH KEY AND CLIP<br>SLOT P/N  |                               |                    |                         |         |
| 2077781112                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 1                       | RED     |
| 2077781212                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 2                       | NATURAL |
| 2077781312                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 3                       | GRAY    |
| 2077781412                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 4                       | YELLOW  |
| 2077781512                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 5                       | BROWN   |
| 2077781612                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 2                  | 6                       | ORANGE  |
|                                                                                                                   |                               |                    |                         |         |
| 2077781113                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 1                       | RED     |
| 2077781213                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 2                       | NATURAL |
| 2077781313                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 3                       | GRAY    |
| 2077781413                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 4                       | YELLOW  |
| 2077781513                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 5                       | BROWN   |
| 2077781613                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 3                  | 6                       | ORANGE  |
|                                                                                                                   |                               |                    |                         |         |
| 2077781114                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 1                       | RED     |
| 2077781214                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 2                       | NATURAL |
| 2077781314                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 3                       | GRAY    |
| 2077781414                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 4                       | YELLOW  |
| 2077781514                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 5                       | BROWN   |
| 2077781614                                                                                                        | UL1015 / UL1230 OR EQUIVALENT | 4                  | 6                       | ORANGE  |

|                                                                                                                                                                                                                                                                                                                                 |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |  |                                                                                                                                                                                                                                                                                                                                                                                                     |  |                  |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |  |  |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|
| FUNCTIONAL SYMBOLS<br> = 0<br> = 0<br> = 0<br>DIVISIONAL SYMBOLS |  | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION<br>DIMENSION UNITS: <b>mm</b> SCALE: <b>1:1</b><br>CURRENT REV DESC: RE-RELEASED FOR CONVERSION ISSUE.<br>GENERAL TOLERANCES (UNLESS SPECIFIED)<br>ANGULAR TOL    ±    °<br>4 PLACES    ±<br>3 PLACES    ±<br>2 PLACES    ±<br>1 PLACE    ±    0.3<br>0 PLACES    ±<br>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS |  | EC NO: 760095<br>DRWN: GOOLAM    2023/08/02<br>CHK'D: GOOLAM    2023/08/18<br>APPR: MRAMAKRISHNA    2023/08/18<br>INITIAL REVISION:<br>DRWN: MUM    2019/01/30<br>APPR: NCSR    2019/07/03<br>THIRD ANGLE PROJECTION<br>  |  | E-SIZE    207778 |  | <div> <div>  </div> <div>           PLUG ASSEMBLY<br/>           SQUBA 3.6         </div> </div> PRODUCT CUSTOMER DRAWING<br>DOCUMENT NUMBER    DOC TYPE    DOC PART    REVISION<br><div> <div>2077780000-SD</div> <div>PSD</div> <div>000</div> <div>D3</div> </div> MATERIAL NUMBER    CUSTOMER    SHEET NUMBER<br><div> <div>SEE TABLE</div> <div>GENERAL MARKET</div> <div>4 OF 4</div> </div> |  |  |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|