


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP	11JUN2023	ED	WH



CONN 1
FEMALE STR
CODE Z WATER BLUE
WITH CLIP SLOT
UNSEALED

CONN 2
FEMALE STR
CODE Z WATER BLUE
WITH CLIP SLOT
UNSEALED

TE P/N	L(mm)	REV
2081384-1	300+10/-0	A
2081384-2	600+10/-0	A
2081384-3	1000+15/-0	A
2081384-4	2000+20/-0	A
2081384-5	3000+30/-0	A
2081384-6	5000+40/-0	A

NOTES:

1. ALL RF CONNECTORS MUST BE ASSEMBLED PER MANUFACTURER'S APPLICATION SPECIFICATIONS WITH FOLLOWING [SC]:
1.1: SOCKET CONTACTS CRIMP HEIGHT
1.2: FERRULES' CRIMP HEIGHT
1.3: CONNECTORS TO COAX CABLE RETENTION FORCE
2. 100% IN-PROCESS ELECTRICAL TEST:
2.1: DC CONTINUITY, FOR CENTER AND OUTER CONDUCTORS, POINT TO POINT
2.2: SHORT CIRCUITS;

3. TEMPERATURE RANGE: -40°C TO 85°C

4. LABEL CONTENT:

TE P/N: XXXXXX-X REV: X
DATE: YYYYMMDD

-X: FOLLOW DRAWING REVISION
-X: -1 OR -2 OR-3
DESCRIPTION:
YYYY: YEAR (EXAMPLE: 2016) MM:
MONTH (EXAMPLE: 02)
DD: DATE (EXAMPLE: 25)

AR	MM	TEAR TAPE FOR PACKAGING	8
1	PC	ID LABEL	7
AR	MM	RTK031L COAXIAL CABLE	6
2	PC	OUTER FERRULE	5
2	PC	SUBASSY FEMALE	4
2	PC	CENTER CONTACT FEMALE	3
2	PC	RETAINER	2
2	PC	FAKRA HSG FEMALE 1P CODE Z	1
-X	U/M	DESCRIPTION	ITEM
QTY			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Z.Z.ZHONG 23FEB2023		 TE Connectivity	
		CHK ERIC.DAI 23FEB2023			
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME — FAKRA STR FEMALE TO FAKRA STR FEMALE WITH CLIP SLOT RTK031 CODE Z	
		APVD WENKE.HE 23FEB2023			
		PRODUCT SPEC —			
		APPLICATION SPEC —			
MATERIAL —		FINISH —		WEIGHT —	
		CUSTOMER DRAWING		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO C=2081384	
				RESTRICTED TO —	
				SCALE —	
				SHEET 1 of 1	
				REV A	