




NOTES:

- ALL RF CONNECTORS MUST BE ASSEMBLED PER MANUFACTURER'S APPLICATION SPECIFICATIONS WITH FOLLOWING [SC]:
1.1: SOCKET CONTACTS CRIMP HEIGHT
1.2: FERRULES' CRIMP HEIGHT
1.3: CONNECTORS TO COAX CABLE RETENTION FORCE
- 100% IN-PROCESS ELECTRICAL TEST:
2.1: DC CONTINUITY, FOR CENTER AND OUTER CONDUCTORS, POINT TO POINT
2.2: SHORT CIRCUITS;
- TEMPERATURE RANGE: -40°C TO 85°C
- MAX FREQUENCY IS 3GHz

5. LABEL CONTENT:

TE P/N: XXXXXX-X REV: X

DATE: YYYYMMDD

X: FOLLOW DRAWING REVISION

X: -1 OR -2 OR-3

DESCRIPTION:

YYYY: YEAR (EXAMPLE: 2016) MM:

MONTH (EXAMPLE: 02)

DD: DATE (EXAMPLE: 25)

TE P/N	LENGTH L(mm)
2081345-1	300 ⁺¹⁰ ₀
2081345-2	600 ⁺¹⁰ ₀
2081345-3	1000 ⁺¹⁵ ₀
2081345-4	2000 ⁺²⁰ ₀
2081345-5	3000 ⁺³⁰ ₀
2081345-6	5000 ⁺⁵⁰ ₀

			1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	LABEL	4
			5m	3m	2m	1m	0.6m	0.3m	COAXIAL CABLE RG58LL	3
			1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	SMA PLUG,RG58 CABLE	2
			1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	FAKRA JACK CODE Z WATER BLUE,RG58 CABLE	1
			2081345-6	2081345-5	2081345-4	2081345-3	2081345-2	2081345-1	DESCRIPTION	ITEM
QUANTITY										

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN ED 24MAR2023

CHK RZ 24MAR2023

APVD WH 24MAR2023

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

CABLE ASSEMBLY, RG58LL CABLE, FAKRA FEMALE CODE Z TO SMA MALE. LENGTH IS L

SIZE A2

CAGE CODE 00779

DRAWING NO C-2081345

RESTRICTED TO -

SCALE -

SHEET 1 OF 1

REV A