




NOTES

1. 材料及び仕上げ(めっき仕様) : TABLE 1 参照
MATERIAL AND FINISHES : SEE TABLE 1
2. 適合ハウジング : 214719シリーズ
APPLICABLE HOUSING : 214719 SERIES
3. 図示の斜線部の範囲は接点部の為、傷、打痕、汚れなどを付けないようにして下さい。
PLEASE DON'T DAMEGE, DON'T DENT, AND DON'T MAKE IT DIRTY,
BECAUSE THE SHADED PORTION SHOWN IN FIGURE IS THE CONTACT AREA.
4. 本製品は金めっき品である。
錫めっき品は2147200000-SD/PSD/000を参照ください。
THIS PRODUCT IS GOLD PLATED
PLEASE REFER TO 2147200000-SD/PSD/000 FOR TIN PLATED.



SECTION Z-Z SECTION Y-Y




トレードマーク及び金型番号
TRADE MARK AND DIE MARK

1 TABLE 1

部品 PART	材質 MATERIAL	
ターミナル TERMINAL	銅合金 COPPER ALLOY	
	接点部 CONTACT	金めっき : 0.1 MICROMETER MINIMUM GOLD PLATING
	下地めっき UNDER PLATING	ニッケルめっき(下地):1.0 MICROMETER MINIMUM NICKEL (UNDER PLATING)
DOCUMENT STATUS	P1	RELEASE DATE 2023/07/20 04:45:32

0.79	0.9	0.71	0.9	0.84	0.65	Φ0.44-0.5mm	AWG #30 -32	リール REEL	214720 5011	連鎖状 CHAIN
0.86	1.0	0.82	0.95	0.94	0.76	Φ0.5-0.6mm	AWG #28 -30		214720 5010	
F	E	D	C	B	A	絶縁被覆外径範囲 INS. RANGE	適合電線範囲 WIRE RANGE	梱包形態 PACKAGING	発注番号 ORDER No.	端子形状 FORM

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:		molex									
mm		NTS													
GENERAL TOLERANCES (UNLESS SPECIFIED)				ZERO-HACHI 0.8WTB CRIMP TERM GOLD PLATING											
ANGULAR TOL ± 3.0 °															
4 PLACES		± 0.2		EC NO: 747483		PRODUCT CUSTOMER DRAWING									
3 PLACES		± 0.2		DRWN: HKOBAYASHI 2023/03/06											
2 PLACES		± 0.2		CHK'D: AIDA 2023/07/20											
1 PLACE		± 0.2		APPR: SAKIYAMA 2023/07/20		DOCUMENT NUMBER 2147200000-SD									
0 PLACES		± 0.2		INITIAL REVISION: DRWN: HKOBAYASHI 2023/03/06						DOC TYPE		DOC PART		REVISION	
APPR: SAKIYAMA 2023/07/20						PSD		001		A					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		214720				GENERAL		1 OF 2	

