

ON/OFF
POWER SWITCH

1783.08 mm
[70.200 in]

41.05 mm
[1.616 in]

265.62 mm
[10.458 in]

76.20 mm TYP
[3.000 in]

27.05 mm TYP
[1.065 in]

SECTION A-A
(VIEW FROM FRONT)

RESETABLE
CIRCUIT
BREAKER

15' FOOT LOCKING
POWER CORD
(NEMA L5-15P)

29.18 mm
[1.149 in]

5.08 mm
[0.200 in]

ASSEMBLY - VIEW FROM END

1789.99 mm
[70.472 in]

ASSEMBLY - VIEW FROM SIDE

ISOMETRIC VIEW

1587H19D1

Finish - Case - Anodized Aluminum Extrusion

Ends - ABS Plastic

Rated - 125 VAC, 60 Hz, 15 Amps

Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)

- UL Listed Standard UL1363

Accessories Included

Mounting Bracket Kit with Hardware



HAMMOND
MANUFACTURING™

1587H19D1

www.hammondmfg.com