




RESETTABLE CIRCUIT
BREAKER




ASSEMBLY - VIEW FROM FRONT




ASSEMBLY - VIEW FROM BOTTOM



SECTION A-A



ISOMETRIC VIEW



ASSEMBLY - VIEW FROM SIDE

1582T6C1
Finish - Front - ASA 61 Grey Painted Steel
Back - ASA 61 Grey Painted Steel
Rated - 125 VAC, 60 Hz, 15 Amps
Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)
- UL Recognized Standard UL1363



HAMMOND
MANUFACTURING™

1582T6C1

www.hammondmfg.com