







SECTION A-A
(VIEW FROM FRONT)



ASSEMBLY - VIEW FROM SIDE




ASSEMBLY - VIEW FROM END



ISOMETRIC VIEW

1585H10A1S
Finish - Case - Anodized Aluminum Extrusion
Ends - ABS Plastic
Rated - 125 VAC, 60 Hz, 15 Amps
Approvals - cULus Listed to: UL1449 & C22.2 No. 269.3-17
Surge Specs - 1080 Joules, 75000 Amps Transient Current
- 500V Voltage Protection Rating (VPR)
Accessories Included
Mounting Bracket Kit with Hardware



HAMMOND
MANUFACTURING™
1585H10A1S
www.hammondmfg.com