




**END VIEW** 





**SECTION B-B** 

SIDE VIEW



CUL US LISTED
FILE #E65324
NEMA 4, 4X, 6, 6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory (modshop@hammfg.com) for quotes
Solid models of this enclosure available in .stp or .x\_t
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

## NOTE

Purchased assembly includes box, lid, silicone gasket, 4 cover screws and 2 ground screws with washers. Box and lid are made from Diecast Aluminum Alloy.

## Recommended cover screw Torque 6.6-8.8 lbf.in (75-100 cN.m)

1590Z062	
1590Z062 Enclosure	
Natural Enclosure	1590Z062
Black Enclosure	1590Z062BK
Grey Enclosure - RAL7001 Gloss	1590Z062GY
ACCESSORIES	
Pre-Formed Silicone Gasket (2 Pack)	1590Z062G
Ground Hardware (50 Pack) [Copper #6-32X5/16 Self-Tapping / #6 Bronze lock Washer]	SCG060-50
Stainless Steel Cover screws (50 pkg) [M4 - 0.7 x 20mm]	SC1550Z103-50



92.05 74.45 [2.93] 19.53 [.77] C -HAMMOND 12.53 [.49] 36.00 50Z103/90Z062 [1.42] 58.05 [2.29] 86.00 [3.39] 32.45 [1.28]

**INSIDE BOX** 

ACCEPTS M4 - 0.7


MACHINE SCREW

C

**ACCEPTS** 

#6 SELF-TAPPING

**GROUND SCREW** 



SECTION C-C MOUNTING HOLE

Dimensions: mm [inches]