

ON/OFF  
POWER SWITCH

1783.08 mm  
[70.200 in]

265.62 mm  
[10.458 in]

76.20 mm TYP  
[3.000 in]

27.05 mm TYP  
[1.065 in]

41.05 mm  
[1.616 in]

SECTION A-A  
(VIEW FROM FRONT)

RESETABLE  
CIRCUIT  
BREAKER

6' FOOT LOCKING  
POWER CORD  
(NEMA L5-15P)

29.18 mm  
[1.149 in]

5.08 mm  
[0.200 in]

ASSEMBLY - VIEW FROM END

1789.99 mm  
[70.472 in]

ASSEMBLY - VIEW FROM SIDE

ISOMETRIC VIEW

1587H19C1

Finish - Case - Anodized Aluminum Extrusion

Ends - ABS Plastic

Rated - 125 VAC, 60 Hz, 15 Amps

Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)

- UL Listed Standard UL1363

Accessories Included

Mounting Bracket Kit with Hardware



HAMMOND  
MANUFACTURING™

1587H19C1

www.hammondmfg.com