







316 STAINLESS
STEEL HINGE
PIN

(2) EACH #10-32 BRASS INSERTS,
AND 316 STAINLESS STEEL
CAPTIVE COVER TAMPER PROOF
SCREWS WITH RETAINING O-RING





OPENING SIZE
HMI120

.321 [8.15] X 45°
TYP. 4x




FIP
POLYURETHANE
GASKET

FIP
POLYURETHANE
GASKET



MATERIAL:
BOX - INJECTION POLYCARBONATE
STANDARD COVER - INJECTED POLYCARBONATE
CLEAR COVER: INJECTED POLYCARBONATE

NOTE:
1. DATA SUBJECT TO CHANGE
2. WILL FIT ENCLOSURE
SIZES 14 X12 AND LARGER



PART No. PJHMI1210HTP

for more information visit
www.hammfg.com
Data subject to change without notice
Drawing Not to Scale