



DIMENSIONS:	
A	3.250" ± 0.063
B	1.615" ± 0.125
C	1.995" ± 0.063
D	2.813" ± 0.063
G	0.187" ± 0.015



NOTE: ALL LEADS ARE 5" MIN. LONG OUT.
CLASS B (130°C) INSULATION
RoHS & REACH COMPLIANT
OPERATING TEMPERATURE: -40°C TO 105°C
STORAGE TEMPERATURE: -40°C TO 85°C

ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
INDUCTANCE	@ 2V, 60Hz, 4A DC, BLK - BLK	6mH	$\pm 15\%$
DCR	@ 20°C, BLK - BLK =	0.133 Ω	$\pm 15\%$
HIPOT	PRIMARY - SECONDARY	2500V, 60Hz, 1 SEC	



**HAMMOND
MANUFACTURING**
ELECTRONIC DIVISION
52 RANKIN PLACE,
WATERLOO, ONTARIO, N2J 3Z5
PH # (519) 886-6181
FAX # (519) 886-9540

TITLE

CHOKE

NO	DATE	REVISION	DWG. BY
0	04/05/18	RELEASED.	C.I.
			DATE
			04/05/18
			DIM IN(X)MM()

157E