




Part No.	Cable color
~04*1TV~	WHITE
~04*2TV~	BLACK

NOTE ① We indicate the length of the harness on the last of product name, 'L' part.


② Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

③ Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 500$, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



For stable supply of this series,
material supplier of piece part#1
will be changed during 2019-2022.
Please note this change in advance.
There will be no difference in product
performance and quality. ①

1	U. FL-LP(V)-040HF(06)	CL331-0559-9-06	2	0.81 Dia. coaxial cable	HALOGEN FREE		
NO.	PART NO.	CODE NO.	NO.	PART NO.			
UNITS mm		SCALE FREE	COUNT ① 2	DESCRIPTION OF REVISIONS DIS-D-00003761	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 20181217
HIROSE ELECTRIC CO., LTD.		APPROVED	① NK. NINOMIYA	20180607	DRAWING NO. PART NO. UFL-2LPVHF6-04**TV-A-L ① CODE NO. ① 1/1		
		CHECKED	① MT. KANEKO	20180606			
		DESIGNED	① MS. MATSUMOTO	20180606			
		DRAWN	① MS. MATSUMOTO	20180606			