


TABLE 1		INSERTION LOSS (MAX dB)	VSWR DC ~ 40GHz
MODEL NUMBER	LENGTH		
415-0542-MM100	100mm +4/-0	-2.3	1.33
415-0542-MM200	200mm +5/-0	-3.2	1.33
415-0542-MM500	500mm +10/-0	-5.5	1.33
415-0542-M1.0	1000mm +15/-0	-9.9	1.33

REV	ECO	DATE
1	INITIAL RELEASE	02-01-2023



- NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS FOR A PERIOD OF ONE MINUTE.
 2. CABLE ASSEMBLIES TO BE 100% TESTED FOR VOLTAGE AND CONTINUITY.

 This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.	Model No: 415-0542-MXXXX		JOHNSON	
	RoHS ☒ (EU)/2015/863 COMPLIANT	Cage Code 34078	Title: CABLE ASSY, METRIC, STR SMP JACK TO STR 2.92MM PLUG, .047" FLEXIBLE CABLE	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH .XX ± .01 .XXX ± .003 .XXXX ± .0010 ANGLE ± 2°	3RD ANGLE PROJECTION Drawn by: TOMMY REN Date: 02-01-2023	Drawing No. 415-0542-MXXXX	REV. 1
	Size A	DO NOT SCALE DRAWING	Workmanship Std: NONE	Sheet 1 OF 1