


6		5			4	3		2		1	
ITEM	PART#	DESCRIPTION			QTY	UOM		FROM	TO	DESCRIPTION	COLOUR
A	2078410002	RECEPTACLE HOUSING FOR L1NK 250 - 1X2 Ck			1	PC		A1	--	1X22AWG DISC PVC BK UL1569	BLACK
B	466261305	CRIMP TERMINAL FOR L1NK 250 - 22-24 AWG			2	PC		A2	--	1X22AWG DISC PVC BK UL1569	BLACK
C	--	WHITE PART ID LABEL			1	PC					



NOTES

- 1.THE PRODUCT MUST MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004.
- 2.CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
- 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
- 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
- 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
- 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
- 7.THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 1.0 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
02/22/2023	B	INITIAL RELEASE	THANUB
DOCUMENT STATUS	P1	RELEASE DATE	2023/03/23 11:04:43

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
FUNCTIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 743463 DRWN: THANUB 2023/02/23 CHK'D: SKUMAR07 2023/03/23 APPR: SKUMAR07 2023/03/23				molex								
	mm		NTS														
	GENERAL TOLERANCES (UNLESS SPECIFIED)								SEE TABLE								
	ANGULAR TOL ± °																
DIVISIONAL SYMBOLS	4 PLACES		±		INITIAL REVISION: DRWN: THANUB 2023/02/20 APPR: SKUMAR07 2023/03/23				PRODUCT CUSTOMER DRAWING								
	3 PLACES		±														
	2 PLACES		±														
	1 PLACE		±														
	0 PLACES		±														
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
						A4-SIZE		224090		2240901020		PSD		000		B	
										SEE TABLE		GENERAL MARKET		1 OF 1			