





Part no. 09 33 000				Ø	Wire gauge		Stripping length	Recommended crimping tool
K+		K-			mm ²	AWG		09 99 000 0888
male contact	female contact	male contact	female contact					
6362	6462	6363	6463	1,15	0,5	20	7,6	
6364	6464	6365	6465	1,48	1	18		
6366	6466	6367	6467	1,78	1,5	16		

  All Dimensions in mm Original Size DIN A4		Scale 2:1		Free size tol.		Ref.	
						Sub.	
 All rights reserved Department EL PD		Created by HOLLERT		Inspected by RIEPE		Standardisation SAP_WFRT	
						Date 2022-03-08	
						State Final Release	
HARTING D-32339 Espelkamp		Title Han E Thermocouple contacts (Type K)					Doc-Key / ECM-Nr. 100824281/UGD/004/B 500000109075
		Type TB	Number 09 33 000 6X6X				Rev. B
							Page 1/1