


6		5		4	
ITEM	PART#	DESCRIPTION		QTY	UOM
A	347910080	MINI50 CONN RCPT 8CKT NB BLK POL A		1	PC
B	5600230421	CTX50 RCPT TERM SN M-GRIP D WIND		8	PC
C	--	WHITE PART ID LABEL		1	PC

2		1	
FROM	TO	DESCRIPTION	COLOUR
A1	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A2	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A3	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A4	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A5	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A6	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A7	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A8	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240511082	Mini50 R-S 8ckt 150mm disc Sn	150±5	15
2240511083	Mini50 R-S 8ckt 300mm disc Sn	300±5	15
2240511084	Mini50 R-S 8ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

- NOTES
- 1.THE PRODUCT MUST MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004.
 2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
 - 7.THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 0.90 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
03/30/2023	B	INITIAL RELEASE	THANUB
DOCUMENT STATUS	P1	RELEASE DATE	2023/05/18 06:16:28