








LEGEND ◆ = KEY PRODUCT CHARACTERISTICS




ISO VIEW




MIN MOUNTING PITCH  
SCALE 1:1



SCHEMATIC CHART



PANEL CUT OUT  
REAR VIEW



PCB-LAYOUT  
COMPONENT SIDE  
TOLERANCE: ± 0.05mm [.002"]

|                                               |             |                                                                                                                                                                 |        |                           |       |                                                                                  |                                                                            |
|-----------------------------------------------|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|---------------------------|-------|----------------------------------------------------------------------------------|----------------------------------------------------------------------------|
| UNLESS OTHERWISE SPECIFIED<br>TOLERANCE TO BE |             | THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.<br>. NO PART THEREOF MAY BE REPRODUCED AND USED<br>WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER |        |                           |       | Amphenol Amphenol Australia Pty.Ltd,<br>22 Industry Blvd, Carrum Downs, VIC 3201 |                                                                            |
| LINEAR                                        | ANGULAR     | MATERIAL:<br><b>REFER TO COMPONENT</b>                                                                                                                          | DRN:   | MH                        | DATE: | 21-12-17                                                                         | TITLE:<br><b>AC3FBH2-AU-PRE<br/>HORIZONTAL FEMALE<br/>CUSTOMER DRAWING</b> |
| X ± 0.5                                       | X' ± 1      |                                                                                                                                                                 | CKD:   | MH                        | DATE: | 21-12-17                                                                         |                                                                            |
| X.X ± 0.2                                     | X.X' ± 30'  |                                                                                                                                                                 | APP'D: | PM                        | DATE: | 21-12-17                                                                         |                                                                            |
| X.XX ± 0.1                                    | X.XX' ± 15' | FINISH: <b>REFER TO COMPONENT</b>                                                                                                                               | SCALE: | 2:1                       | SIZE: | A3                                                                               | PART No:<br><b>AC3FBH2-AU-PRE</b>                                          |
| BREAK ALL SHARP EDGES<br>AND REMOVE ALL BURRS |             | DO NOT SCALE                                                                                                                                                    |        | DIMENSIONS IN MILLIMETRES |       | CAD FILE 55011280000220                                                          | DRAWING NO.<br><b>55011280-000-2</b>                                       |
|                                               |             |                                                                                                                                                                 |        |                           |       |                                                                                  | SHEET<br><b>2 / 2</b>                                                      |