




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
1		PROPOSED	19NOV2020	-	-
2		REVISED PANEL CUT-OUT	14MAY2021	DF	DR
3		ADD DUST CAP	02JUL2021	CG	DR
4		ADD NICKEL PTFE ASSEMBLIES	30JAN2023	CG	DR
A		RELEASED PER ECN-23-223284	26JULY2023	MM	DR




- 1 FINISH: OLIVER DRAB, CADMIUM.
- 2 FINISH: NICKEL, ELECTROLESS
- 3 REFERENCE MIL-DTL-38999 SPECIFICATION FOR PANEL NUT INSTALLATION TORQUE VALUE.
- 4 FINISH: NICKEL PTFE

45 DEGREE
INSERT OPTION



RECOMMENDED PANEL CUT-OUT 3



KEYING ORIENTATION DETAIL

KEYING ORIENTATION	A	B	C	D
N	95°	141°	208°	236°
A	113°	156°	182°	292°
B	90°	145°	195°	252°

NICKEL PTFE 4	B	45°	1-2379812-8
NICKEL PTFE 4	B	-	1-2379812-7
NICKEL PTFE 4	A	45°	1-2379812-6
NICKEL PTFE 4	A	-	1-2379812-5
NICKEL PTFE 4	N	45°	1-2379812-4
NICKEL PTFE 4	N	-	1-2379812-3
NICKEL 2	B	45°	1-2379812-2
NICKEL 2	B	-	1-2379812-1
OLIVE DRAB 1	B	45°	1-2379812-0
OLIVE DRAB 1	B	-	2379812-9
NICKEL 2	A	45°	2379812-8
NICKEL 2	A	-	2379812-7
OLIVE DRAB 1	A	45°	2379812-6
OLIVE DRAB 1	A	-	2379812-5
NICKEL 2	N	45°	2379812-4
NICKEL 2	N	-	2379812-3
OLIVE DRAB 1	N	45°	2379812-2
OLIVE DRAB 1	N	-	2379812-1
FINISH (SHELL AND NUT)	KEYING ORIENTATION SEE DETAIL	INSERT ORIENTATION	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DATE: 19NOV2020
DWN: D. FABIAN
CHK: -
APVD: -

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±
ANGLES ±1
FINISH -

MATERIAL: -

PRODUCT SPEC

APPLICATION SPEC

WEIGHT: -

CUSTOMER DRAWING

NAME: KIT, RECEPTACLE CONNECTOR ASSEMBLY FIBER OPTIC, MT, SIZE 15, 4 CAVITY 38999 STYLE, PANEL MOUNT

SIZE: A | CAGE CODE: 00779 | DRAWING NO: 2379812

RESTRICTED TO: -

SCALE: 2:1 | SHEET: 1 OF 1 | REV: A

TE Connectivity

TE